PRODUCT-DETAILS

HSB500-C

SHRINK KON BOX - 6M TRANSP.



General Information

Extended Product Type	HSB500-C
Product ID	7TCA017300R0366
EAN	5414363104445
Catalog Description	SHRINK KON BOX - 6M TRANSP.
Long Description	Thin Wall Heat Shrink Tubing in Dispenser Box - 1/2 Inch Expanded Inside Diameter - 6.0 Meters Transparent

Ordering

EAN	5414363104445
UPC	786210564197
Country or Territory of Origin	Germany
Selling Unit of Measure	each

Dimensions

Product Net Depth /	19.68 in

© 2025 ABB. All rights reserved.

Downloaded from Arrow.com.

Length	6 m

Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	2.4 in 61 mm
Package Level 1 Height	6.7 in 170 mm
Package Level 1 Depth / Length	6.7 in 170 mm
Package Level 2 Units	60 piece
Package Level 2 Width	15.8 in 401 mm
Package Level 2 Height	22.5 in 572 mm
Package Level 2 Depth / Length	20.9 in 531 mm

Environmental

RoHS Status	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
REACH Information	False - does not contain substances > 0.1 mass percentage

Additional Information

Brand / Label	Shrink-Kon
Color	Transparent
Dielectric Test Voltage	280/Mil (11kV/mm) V
Effective Date	19980621
Flammability Hazard Rating	Self Extinguishing
Process Temperature Rating	-67 to +212 °F -55 to +100 °C
Product Name	Plastic conduit
Product Type	Thin-Wall Heat Shrinkable Tubing
RoHS Date	9AKK107992A8965
Shrink Ratio	2:1
Shrink Temperature	230 °F 110 °C
Thickness	Thin
Water Absorption	0.03%

External Classifications and Standards

ETIM 7	EC000217 - Shrink tubing
ETIM 8	EC000217 - Shrink tubing
ETIM 9	EC000217 - Shrink tubing
UNSPSC	39121723
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5073 >> Heat shrinkable tube

© 2025 ABB. All rights reserved.

Downloaded from Arrow.com.

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Identification & Heat Shrink



© 2025 ABB. All rights reserved.

Downloaded from Arrow.com.