



BIBD42FX, Double Sided Flex Rated Two Conductor Clear Insulated Mult-Tap Connector

By Burndy
Catalog # [BIBD42FX](#)



Aluminum UNITAP, Double Sided Entry, #14-#4 Class B & C ,#14-#6 Class G,H,I,K, DLO, 2 PORT.

Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory
- Suitable for Code and Flex Conductor
- Color-coordinated conductor port caps display wire range and classes of conductor accepted
- Screw port caps show installation torque information for easy reference

Application

Tap connections and in-line splice/reductions are made quickly and easily with the UNITAP™ line of connectors

General

Catalog Number	BIBD42FX
Connector Type	Multi Tap
EU RoHS Indicator	Yes
Insulation	Y
Material	Aluminum
Number Of Ports	2
Plated	Y
Plating Type	Tin
Sub Brand	UNITAP
Temperature Rating	-40° C to 135 °C
Trade Name	UNITAP™
Type	BIBD, Multi-Port
UPC	621945438705
UPC 14 Digit GTIN	00621945438705

Dimensions

Dimension - Height mm	0 mm
Dimension - Length Overall	.83 in
inch	

Electrical Ratings

Amperage Rating	310 A
Voltage - Maximum	600 V

Conductor Related

Conductor Size	14-4 AWG
Conductor Type	• AL C Str-Size • CU C Str-Size

Certifications And Compliance

Industry Standard(s)	UL 486A-486B
Standards - Industry Standards	UL 486A-486B
Met	
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - UNITAP™ Products](#)
[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50046931](#)
[Specifications - BIBD42FX](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
BRDY-BIBD42FX-SPEC-EN | REV 7/2025