


NOTES:

A. MATERIAL:
1. JACK HOUSING : ZINC ALLOY.
2. IDC MODULE : POLYCARBONATE (PC)
3. IDC CONTACT : COPPER ALLOY
4. JAW : ZINC ALLOY
5. CLIP : ZINC ALLOY.

B. FINISH:
1. CONTACTS: 50 micro-inch OF GOLD OVER 70 TO 100 micro-inch OF NICKEL.
2. HOUSING: NICKEL PLATING

C. PACKAGING:
1. PACKAGING: JACKS ARE PACKED INDIVIDUALLY ALONG WITH CABLE TIE IN POLY BAG WITH LABEL.
2. PRODUCT PACKAGING LABEL CONTAINS QR CODE FOR INSTALLATION INSTRUCTIONS.

PART NUMBER TABLE		
MPN NO.	SAP NO.	DESCRIPTION
KSJ-00079	183010070	JACK KEYSTONE CAT 6A SHIELDED



ISO VIEW
SCALE 2:1

DOCUMENT STATUS	P1	RELEASE DATE	2024/11/29 12:03:17

Downloaded from Arrow.com.

FUNCTIONAL SYMBOLS
FA = 0
FC = 0
FD = 0
DIVISIONAL SYMBOLS

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS	SCALE
mm	1:1

GENERAL TOLERANCES (UNLESS SPECIFIED)

ANGULAR TOL	± 0.5 °
4 PLACES	±
3 PLACES	±
2 PLACES	±
1 PLACE	± 0.5
0 PLACES	±

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

CURRENT REV DESC:

EC NO: 796497
DRWN: PBANDI 2024/08/30
CHK'D: NKUMAR02 2024/11/29
APPR: NKUMAR02 2024/11/29

INITIAL REVISION:
DRWN: NBP 2015/06/26
APPR: RCG 2015/08/07

THIRD ANGLE PROJECTION | DRAWING: A3-SIZE | SERIES: 18301

molex

JACK KEYSTONE TOOL LESS CATEGORY 6A SHIELDED

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION
SD-18301-030	PSD	001	B

MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
SEE TABLE	GENERAL MARKET	1 OF 1