

Thermofit® Molded Parts

Specification Control Drawing

Part Number: 202B521 thru 598
Description: Boot, Connector Protector

Notes:

1. All dimensions are in $\frac{\text{Inches}}$
[Millimeters]
2. Dimensions appearing in table are as follows:
a - as supplied
b - after unrestricted recovery
3. Part number 202B521 does not have bulb section.





Table of Dimensions

Part Number	H		J		K		P	R	S	KO	KW
	Min a	± 5% b	Min a	Max b	Min a	Max b	± 10% b	± 10% b	± 10% b	± 10% b	± 20% b
202B521	.99 [25,1]	.99 [25,1]	See Note Three		.99 [25,1]	.22 [5,6]	3.26 [82,8]	See Note Three	2.00 [50,8]	.83 [21,1]	.07 [1,78]
202B532	1.12 [28,4]	1.12 [28,4]	1.12 [28,4]	.72 [18,3]	1.12 [28,4]	.26 [6,6]	4.16 [105,7]	2.90 [73,7]	2.37 [60,2]	.66 [16,8]	.07 [1,78]
202B542	1.26 [32,0]	1.26 [32,0]	1.26 [32,0]	.87 [22,1]	1.26 [32,0]	.28 [7,1]	4.63 [117,6]	3.22 [81,8]	2.37 [60,2]	.70 [17,8]	.08 [2,03]
202B553	1.44 [36,6]	1.44 [36,6]	1.44 [36,6]	1.06 [26,9]	1.44 [36,6]	.33 [8,4]	5.81 [147,6]	3.92 [99,6]	3.09 [78,5]	1.06 [26,9]	.08 [2,03]
202B563	1.69 [42,9]	1.69 [42,9]	1.69 [42,9]	1.33 [33,8]	1.69 [42,9]	.39 [9,9]	6.80 [172,7]	4.66 [118,4]	3.09 [78,5]	1.11 [28,2]	.08 [2,03]
202B574	2.03 [51,6]	2.03 [51,6]	2.03 [51,6]	1.67 [42,4]	2.03 [51,6]	.62 [15,7]	7.96 [202,2]	5.02 [127,5]	3.46 [87,9]	1.66 [42,2]	.09 [2,29]
202B585	2.57 [65,3]	2.57 [65,3]	2.57 [65,3]	2.09 [53,1]	2.57 [65,3]	.80 [20,3]	9.74 [247,4]	6.07 [154,2]	3.46 [87,9]	2.18 [55,4]	.10 [2,54]
202B596	2.82 [71,6]	2.82 [71,6]	2.82 [71,6]	2.61 [66,3]	2.82 [71,6]	1.05 [26,7]	11.84 [300,7]	7.40 [188,0]	4.19 [106,4]	2.70 [68,6]	.11 [2,79]
202B598	3.50 [88,9]	3.50 [88,9]	3.42 [88,9]	2.61 [66,3]	3.42 [88,9]	1.05 [26,7]	11.84 [300,7]	7.40 [188,0]	4.19 [106,4]	2.70 [68,6]	.11 [2,79]

Raychem

Raychem Corporation
300 Constitution Drive
Menlo Park, California 94025
415) 361 6055

If this document is printed it becomes uncontrolled.
Check for the latest revision.

Revision: L
Date: 8-1-85

Part Number: 202B521 thru 598
Description: Boot, Connector Protector

Thermofit® Molded Parts Specification Control Drawing

Part Number: 202B521 thru 598
Description: Boot, Connector
Protector

Compatability Chart

Material Dash No.	Material Description	RT Spec	Coating Slash No.	Coating S No.	Coating Description
- 3	Polyolefin, Semi-Rigid	RT-301	N/A		
- 4	Polyolefin, Flexible	RT-1304	N/A		
- 6	Silicone, Flame Retarded	RT-602	N/A		
- 25	Elastomer, Fluid Resistant	RT-1325	N/A		

Ordering Information:

202B5XX — XX — XX / XXX

Base part number

Material dash number
(see compatability chart)

Modification number
(if necessary, see front of SCD binder
for a complete modification list)

Adhesive slash number
(if necessary, see compatability chart)

If this document is printed it becomes uncontrolled.
Check for the latest revision.

This drawing is subject to change without notice; consult your nearest field representative for current revision.

Raychem

Raychem Corporation
300 Constitution Drive
Menlo Park, California 94025
415) 361 6055

Revision: **L**
Date: **8-1-85**

Part Number: 202B521 thru 598
Description: Boot, Connector Protector