

Product data sheet

Specifications



Power Cord Kit (6 ea), C19 to C20 (90 degree), 0.6m

AP98892F

⚠ Discontinued on: Oct 4, 2023

⚠ Discontinued

Overview

Presentation	Low profile cord designed to eliminate space interference when accessing removable hot swap blade modules.
Lead time	Usually in Stock

Main

Input Connection Type	IEC 60320 C20
Provided equipment	3 left-angle jumper cords 3 right-angle jumper cords

Physical

Colour	Black
Height	61 cm
Width	11.4 cm
Depth	5.1 cm
Net weight	0.98 kg
Mounting preference	No preference
Mounting mode	Not rack-mountable

Input

Input current limits	16 A
----------------------	------

Output

Number of power socket outlets	1 IEC 60320 C19
--------------------------------	-----------------

Environmental

Ambient air temperature for operation	-5...60 °C
Relative humidity	5...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-25...65 °C
Storage Relative Humidity	5...95 %
Storage altitude	0...15240 m

Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.2 cm
Package 1 Width	21.6 cm
Package 1 Length	15.2 cm
Package 1 Weight	1.068 kg
Unit Type of Package 2	CAR
Number of Units in Package 2	8
Package 2 Height	23 cm
Package 2 Width	33 cm
Package 2 Length	47.2 cm
Package 2 Weight	9 kg
Unit Type of Package 3	PAL
Number of Units in Package 3	8
Package 3 Height	143.99 cm
Package 3 Width	100 cm
Package 3 Length	120 cm
Package 3 Weight	9 kg

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
EU RoHS Directive	Compliant
SCIP Number	1cdb2fed-a06f-4574-913d-8df8e70936b2
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov

Use Again

Repack and remanufacture	
End of life manual availability	End of Life Information
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Image of product / Alternate images

Alternative

