



99M1131-20-0/2/9-0 Product Details




Share



Print



Email



 Active

Spec 99 and Spec 100 Wire and Cable

99M1131-20-0/2/9-0

99M1131-20-0/2/9-0 

TE Internal Number: 7617813001

Product Highlights [View All](#)

- Cable Type = Spec 99M
- Cable Style = Jacketed, Round-Braid Shielded
- Wire Size (AWG or Metric) = 20 AWG [0.62²]
- Number of Conductors = Twisted Triple
- Equipment Wire Application

Pricing & Availability



Request Sample



Add to My Part List



Buy Product through
Distributor



Feedback

Documents

Features

Compliance

Please Note:

Use the Product Drawing for all design activity

Product Type Features

Cable Type	Spec 99M
Cable Style	Jacketed, Round-Braid Shielded

Electrical Characteristics

Wire Size (AWG or Metric)	20 AWG [0.62²]
Voltage Rating (VAC)	600

Dimensions

Conductor Outer Diameter (mm [in])	1.01 [0.040]
Shield (Screen) Diameter (mm [in])	3.46 [0.136]

Body Features

Wire Color	Black, Red, White
Nominal Outside Diameter (mm [in])	4.06 [0.160]
Wire Diameter (mm [in])	1.30 [0.0511]
Cable Jacket Color	Black
Conductor Type	Tin-Coated Copper

Configuration Features

Number of Conductors	Twisted Triple
----------------------	----------------

Industry Standards

RoHS/ELV Compliance 	RoHS compliant, ELV compliant
Lead Free Solder Processes 	Not relevant for lead free process
RoHS/ELV Compliance History	Always was RoHS compliant

Conditions for Usage

Wire Size - Details	20 AWG 0.62 mm², 0.00095 in², 19 x 32 AWG
Temperature Range (°C)	-55 – +125

Operation/Application

Application	Equipment Wire
-------------	----------------

Packaging Features

Wire Source	United Kingdom
-------------	----------------

Other

Brand	Raychem
Node Classification	QUARANTINE

Related Products

Not quite the product you're looking for?

[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Corporate Information

About TE
Investors
News Room
Supplier Portal
Careers
Terms & Conditions
Privacy Policy
Global Accessibility Statement

Quick Links

Distributor Inventory
Product Cross Reference
Documents & Drawings
Product Compliance Support Center
Site Map

Customer Support

Email or Chat With Us
Find a Phone Number
Knowledge Base
Manage Your Account

Keep Me Informed

