

3-5175475-8 Product Details

 Share  Print  Email



 Active

 View 3D PDF

1.27 [.050] Series I, HD, FH and J Connectors

CHAMP 050 B/B REC V W/LEG 68P

3-5175475-8 

TE Internal Number: 3-5175475-8

Product Highlights [View All](#)

- Connector
- Applies To Printed Circuit Board
- Connector Style = Receptacle
- 68 Positions
- 1.27 mm Centerline

Pricing & Availability

Request Sample







Add to My Part List

Buy Product through
Distributor

Feedback

DocumentsFeaturesCompliance


Please Note:
Use the Product Drawing for all design activity

Product Type Features	
Product Type 	Connector
Profile 	Standard
PCB Mount Style	Through Hole
PCB Mount Retention	With
PCB Mount Retention Type 	Boardlock(s)
PCB Mounting Orientation 	Vertical
Type of Connector 	High Density (HD)
PCB Mount Alignment 	Without
Color	Black
Used For	Board To Board Applications
Sealed Bottom	Without
Product Series	Series I


Termination Features	
Termination Post Length (mm [in]) 	3.10 [0.122]


Body Features	
Retention Leg Material	Brass
Retention Leg Plating	Tin over Nickel


Contact Features	
Contact Plating, Mating Area, Material 	Gold (20)
Contact Base Material	Phosphor Bronze

Housing Features	
Connector Style	Receptacle
Centerline (mm [in]) 	1.27 [0.050]
Housing Material	Nylon - GF

Configuration Features	
Number of Positions 	68

Industry Standards	
RoHS/ELV Compliance 	RoHS compliant, ELV compliant
Lead Free Solder Processes 	Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
RoHS/ELV Compliance History	Always was RoHS compliant
UL Flammability Rating	UL 94V-0

Conditions for Usage	
Applies To	Printed Circuit Board
Housing Temperature Rating 	Standard

Operation/Application	
Application 	Standard

Other	
Brand	AMP

Related Products

Not quite the product you're looking for?
[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Corporate Information

About TE
Investors
News Room
Supplier Portal
Careers
Terms & Conditions
Privacy Policy
Global Accessibility Statement

Quick Links

Distributor Inventory
Product Cross Reference
Documents & Drawings
Product Compliance Support Center
Site Map

Customer Support

Email or Chat With Us
Find a Phone Number
Knowledge Base
Manage Your Account

Keep Me Informed

