




CL501, Copper Lay-in Lug, #14-4 AWG, #10 Stud

By Burndy

Catalog # [CL501](#)

Copper Lay-in Lug, Accommodates #14-4 AWG Copper, #10 Stud, UL467 Listed for Direct Burial



Features

- UL467 Listed, Rated for Direct Burial
- Lay-In QIKLUG™ features high strength pure electrolytic copper ensuring maximum strength and conductivity
- Open-faced design allows for fast lay-in of conductor without the need for cutting or breaking

Application

For Direct Burial Applications In Concrete Or Earth, For Fast Lay-In Of The Conductor Without The Need For Cutting Or Breaking

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	Yes
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	• 14 AWG • 12 AWG • 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG
Conductor - Copper Solid Size	• 14 AWG • 13 AWG • 12 AWG • 11 AWG • 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG

- 5 AWG
 - 4 AWG
- | | |
|-------------------------------------|----------------|
| Conductor - Copper Solid Size Range | 14 AWG-4 AWG |
| Conductor Type | CU C Str-Size |
| Conductor - Copper Str Size Range | 14 AWG - 4 AWG |

Dimensions

Package Height	3.000 in
Dimension - Height mm	21.6 mm
Dimension - Height inch	0.85 in
Package Weight	4.590 lb.
Package Length	5.500 in
Package Width	3.800 in
Dimension - L Length Overall mm	29 mm
Dimension - Hole Size mm	6 mm
Dimension - Hole Size inch	0.22 in
Dimension - Stud Size inch	17/64
Dimension - Width mm	10 mm
Dimension - Width inch	0.38 in
Dimension - D inch	0.47 in
Dimension - N inch	0.19 in
Dimension - Length Overall inch	1.13 in

General

Trade Name	QIKLUG™
Plated	N
UPC	781810276150
Type	Open-Faced
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810276150
UPC 14 Digit GTIN	00781810276150

Logistics

Minimum Pack Quantity	1
Pallet Quantity	25600
Carton Quantity	500

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)

