



Quality Products. Service Excellence.

Steel Rack Blanking Panels 14-Gauge Solid Rack Filler Panels *PBPS*

Series

Solid steel rack panels designed to cover unused rack space and improve airflow efficiency in rack systems.

TOP SELLER



Key Features and Benefits

- 14-gauge steel construction provides durable rack space coverage and airflow control in high-density environments.
- Designed to install in unused rack space to improve cooling efficiency and prevent air recirculation.
- Solid panel design blocks airflow gaps, supporting proper front-to-rear cooling.
- Fits standard 19 in EIA-compliant rack rails for universal compatibility.
- Available in multiple heights (1U–10U+) to match rack configurations.
- Smooth powder coat finish provides a clean, professional appearance.
- Multiple color options available to match rack environments.
- Helps improve rack organization and equipment separation.
- TAA-compliant, manufactured in North America within an ISO 9001 certified facility.
- Powder coat finish (GREENGUARD, TSCA, RoHS compliant) supports environmental and durability requirements.

The PBPS Series steel rack blanking panels provide a reliable solution for covering unused rack space while improving airflow and cooling efficiency. Designed with a solid steel construction, they help prevent hot and cold air mixing in rack environments.

By blocking open rack units, the PBPS Series supports proper thermal management, improved system performance, and a clean, organized installation in data centers and network environments.

Where the PBPS Series Works Best

- Data centers and server rooms
- Telecom and network installations
- High-density rack environments
- Hot aisle / cold aisle containment systems
- Wall mount and floor-standing racks

Best Applications for the PBPS Series

- Covering unused rack space to improve airflow
- Preventing hot and cold air recirculation
- Enhancing cooling efficiency in rack systems
- Improving rack organization and appearance
- Supporting thermal management strategies



This product is available for private label. [Click here to learn more.](#)

Accessories

- Hardware for Rack Mounting Solutions

- Rack Rail Reducer Panel 23 to 19 Inch
Rack Adapter Conversion Panel

RAL9005 Matte Black Part No.	ANSI61 Dark Gray Part No.	RAL7035 Light Gray Part No.	RAL9003 Matte White Part No.	Panel Height		Qty of Mounting Points
				Rack Units	Panel Height	
PBPS19001BK	PBPS19001GY2	PBPS19001LG2	PBPS19001WH	1U	1.75	4
PBPS19003BK	PBPS19003GY2	PBPS19003LG2	PBPS19003WH	2U	3.50	4
PBPS19005BK	PBPS19005GY2	PBPS19005LG2	PBPS19005WH	3U	5.25	4
PBPS19007BK	PBPS19007GY2	PBPS19007LG2	PBPS19007WH	4U	7.00	4
PBPS19008BK	PBPS19008GY2	PBPS19008LG2	PBPS19008WH	5U	8.75	4
PBPS19010BK	PBPS19010GY2	PBPS19010LG2	PBPS19010WH	6U	10.50	8
PBPS19012BK	PBPS19012GY2	PBPS19012LG2	PBPS19012WH	7U	12.25	8
PBPS19014BK	PBPS19014GY2	PBPS19014LG2	PBPS19014WH	8U	14.00	8
PBPS19015BK	PBPS19015GY2	PBPS19015LG2	PBPS19015WH	9U	15.75	8
PBPS19017BK	PBPS19017GY2	PBPS19017LG2	PBPS19017WH	10U	17.50	8

Tags: rack blanking panel, steel rack panel, rack filler panel, solid rack panel, server rack blank panel, *Data subject to change without notice*
rack airflow panel, 19 inch rack panel, rack space cover panel

© 2026. Hammond Manufacturing Ltd. All rights reserved.