

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0585500000](#)
Status: **Active**
Overview: [HMC™ Heavy Duty Rectangular Connectors](#)
Description: [HMC™ Rectangular Industrial End Bell Cap Assembly, PG29, 14.00-18.00mm dia. Wire, Blue Bush, for External Threaded Hoods](#)

Documents:

- [3D Model](#)
[Drawing \(PDF\)](#)
[Product Specification PS-500810-001-001 \(PDF\)](#)
[Product Specification PS-54478-001-001 \(PDF\)](#)
[Product Specification PS-58691-004-001 \(PDF\)](#)
- [Application Specification AS-500811-001-001 \(PDF\)](#)
[Application Specification AS-58696-005-001 \(PDF\)](#)
[Application Specification AS-58696-006-001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	I/O Connectors
Series	58550
Application	Panel-Mount, Wire-to-Wire
Component Type	Bell Cap Assembly
Overview	HMC™ Heavy Duty Rectangular Connectors
Product Name	HMC™
Type	N/A
UPC	800753502178

Physical

Boot Color	N/A
Circuits (Loaded)	N/A
Durability (mating cycles max)	50
Gender	N/A
Lock to Mating Part	Yes
Material - Plating Mating	N/A
Net Weight	62930.000/mg
Orientation	N/A
PCB Locator	No
Packaging Type	Bag
Panel Mount	N/A
Pitch - Mating Interface	N/A
Polarized to Mating Part	N/A
Polarized to PCB	N/A
Surface Mount Compatible (SMC)	N/A
Termination Interface: Style	N/A
Waterproof / Dustproof	No


Electrical

Current - Maximum per Contact	35.0A
Shielded	No
Voltage - Maximum	250V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Application Specification	AS-500811-001-001, AS-58696-005-001, AS-58696-006-001
Product Specification	PS-500810-001-001, PS-54478-001-001, PS-58691-004-001
Sales Drawing	SD-58550-****



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Contained Per - ED/108/2014 (17 Dec 2014)

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[58550](#) Series

Use With

58461-*01* Hood, 58462-*01* Hood, 58474-*00* Wire-to-Wire Covers, [58511-0000](#)

This document was generated on 06/29/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION