Part Number : 1601116013
Product Description : MX150 Hybrid Mat-Sealed Female Connector Assembly, Dual Row, 12 Circuits, Keying Option C, with Extended Clipslot, Dark Gray
Series Number : 160111
Status : Active
Product Category : Connector Housings



Documents and Resources

Drawings

1601116013_sd.pdf
1601118000-000.pdf
1601118002-000.pdf
1601119000-000.pdf
PK-31300-903-001.pdf
1601116013_stp.zip

Specifications

1601110001-AS-000.pdf
AS-33611-001-001.pdf
1601110001-PS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant
China RoHS	per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Dodecamethylcyclohexasiloxane; Decamethylcyclopentasiloxane; Octamethylcyclotetrasiloxane per D(2025)7771-DC (04 Feb 2026)

Downloaded from Arrow.com.

EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	160111
Description	MX150 Hybrid Mat-Sealed Female Connector Assembly, Dual Row, 12 Circuits, Keying Option C, with Extended Clipslot, Dark Gray
Application	Power, Wire-to-Wire, Automotive
Comments	No Connector Position Assurance (CPA)
Product Name	MX150
UPC	191128170543

Physical

Circuits (maximum)	12
Color - Resin	Gray (Dark)
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes

Downloaded from Arrow.com.

Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	19.850/g
Number of Rows	2
Packaging Type	Partitioned Carton
Panel Mount	No
Pitch - Mating Interface	3.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
MX150 Hybrid Mat-Sealed, Dual Row, Male Connector Assemblies	160112

Use with Part(s)

Description	Part Number
MX150 Female Terminals	33001
MX150 Female Terminals	33012
Use With	Industry Standard Terminal 2.80mm

Downloaded from Arrow.com.