



© 2021 TE Connectivity. All Rights Reserved.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	AS PER ECR-23-185584	30AUG2023	SSM	WH

















2386586-1

NOTE:

1.MATERIAL SPECIFICATION:
- 1-1.HOUSING :LCP, UL94V-0, BLACK.
- 1-2.CONTACTS: COPPER ALLOY.
- 1-3.SHELL: COPPER ALLOY.

2.PLATING SPECIFICATION:
- 2-1.CONTACTS:
  - Ni 80~150u". UNDER PLATED OVER ALL.
  - Au4u''MIN PLATED ON THE FUNCTIONAL AREA OF CONTACT.
  - Au3~8u'' PLATED ON SOLDER AREA.
- 2-2.SHELL:
  - Ni 80~150u". UNDER PLATED OVER ALL.
  - Au3~8u'' PLATED ON SOLDER AREA.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Jone Ji 05FEB2021	TE Connectivity Ltd.
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 0.4; 1 PLC ± 0.25; 2 PLC ± 0.15; 3 PLC ± 0.1; 4 PLC ± –; ANGLES ± 3	CHK Niki S 05FEB2021	NAME FINE PITCH BTB 8 POS REC – –
MATERIAL –	FINISH –	APVD Niki S 05FEB2021	SIZE A2 / CAGE CODE 00779 / DRAWING NO C-2386586 / RESTRICTED TO –
		PRODUCT SPEC –	
		APPLICATION SPEC –	
		WEIGHT –	CUSTOMER DRAWING / SCALE 8:1 / SHEET 1 OF 3 / REV A1


2386586

1471-9 (1/15)


Downloaded from Arrow.com.

© 2021 TE Connectivity. All Rights Reserved.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	–	SEE SHEET 1	–	—	—




RECOMMEND PCB LAYOUT





RECOMMEND ELECTRICAL CIRCUIT LAYOUT
COPPER FOIL THINCKNESS 1oz
CAN USE MORE THICKNESS SAME
OR BETTER CONDITION LAYOUT



RECOMMEND METAL MASK DIMENSIONS
METAL MASK THICKNESS:80um








THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN — 05FEB2021	TE Connectivity Ltd.
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 0.4; 1 PLC ± 0.25; 2 PLC ± 0.15; 3 PLC ± 0.1; 4 PLC ± –; ANGLES ± 3	CHK — –	NAME: FINE PITCH BTB 8 POS REC — —
MATERIAL –	FINISH –	APVD — –	SIZE A2 · CAGE CODE 00779 · DRAWING NO C-2386586 · RESTRICTED TO —
		PRODUCT SPEC —	
		APPLICATION SPEC —	
		WEIGHT —	CUSTOMER DRAWING · SCALE 8:1 · SHEET 2 OF 3 · REV A1


2386586


Downloaded from Arrow.com.

© 2021 TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	–	SEE SHEET 1	–	—	—







5000	7	35000
PCS/REEL	REEL/BOX	PCS/BOX
(PACKING CAPACITY)		

THIS DRAWING IS A CONTROLLED DOCUMENT.	DWN — 05FEB2021	TE Connectivity Ltd.	
DIMENSIONS: mm	CHK — –	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 0.4; 1 PLC ± 0.25; 2 PLC ± 0.15; 3 PLC ± 0.1; 4 PLC ± –; ANGLES ± 3	APVD — –	FINE PITCH BTB 8 POS REC — —	
MATERIAL –	PRODUCT SPEC —	SIZE A2	CAGE CODE 00779
FINISH –	APPLICATION SPEC —	DRAWING NO C-2386586	RESTRICTED TO —
	WEIGHT —	CUSTOMER DRAWING	SCALE 8:1
		SHEET 3 OF 3	REV A1

2386586

1471-9 (1/15)

Downloaded from Arrow.com.