Part Number : 192050004
Product Description : VersaKrimp Parallel Splice for 8 AWG Wire, Carton
Series Number : 19205
Status : Active
Product Category : Splices
Engineering Part Number : D-355



Documents and Resources

Drawings

192050004_sd.pdf

Specifications

PS-19902-013-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 33
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Splices
Series	19205
Description	VersaKrimp Parallel Splice for 8 AWG Wire, Carton
Product Name	VersaKrimp
Type	Parallel Splice
UPC	800755060843

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed - Brazed
Insulation	None
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.887/g
Packaging Type	Carton
Wire Size (AWG)	8

Application Tooling

Global

Description	Part Number

Downloaded from Arrow.com.

Crimp Head for the AT-200 Pneumatic Hand Tool	192820004
Hand Crimp Tool	192840035
Putt Pump Dieless Head System	192860065
Putt Pump Hydraulic Head Crimper, Die Set Required, For Insulated and Non-Insulated Terminals and Splices	192860117
Die Set (Large) for the HHLS Hydraulic Crimper	192900001
Manual Tool for Crimping Non-insulated 8 AWG thru 4/0 Terminals	192940008
PremiumGrade Hand Crimp Tool for 8-2 AWG Terminals	640013900
RHT1080 Hand Crimp Tool	640034400
Square “DIN” style dies for 8 AWG	640037670
Hand Crimp Tool, Bench Mount	640063900
Crimp Head for the AT-200 Pneumatic Hand Tool	640074400
Putt Pump Dieless Head Crimper, For Insulated and Non-Insulated Terminals and Splices	638162000

Downloaded from Arrow.com.