



JavaScript seems to be disabled in your browser.
You must have JavaScript enabled in your browser to utilize the functionality of this website.

Wiha Tools Canada  selling **Wiha** made hand tools in Canada since 2007



IBEW-NECA
DISCOUNT

Q

 1-866-494-0096  Cart ▾

[Account](#) | [Log In](#) | [Contact Us](#) | [Distributors](#)

 [Wiha Tools No Hassle Guarantee](#)

 Menu

Torx	+
Torque Tools	+
Tech Tools	+
Shop Tools	+
Screwdrivers	+
Pliers	+
Insulated Tools	+
Hex	+
ESD Safe	+
Bits & Sets	+
Best Sellers	

Home → Tool Types → L-Keys → ErgoStar Ball End Hex L-Key Inch 13 Piece Set

ErgoStar Ball End Hex L-Key Inch 13 Piece Set

REF/





Sale



Zoom

Titles and descriptions supersede the photo. We typically use the same image for different sizes of tools.

ErgoStar Ball End Hex L-Key Inch, Chrome-V-Moly Super Tool Steel, Hard Chrome Finish 13 Piece Set in ErgoStar Auto-Open Key Holder .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"

SKU: 66988

Add to Cart

Qty:



Share on Facebook



Tweet This



Pin it

Frequently bought together



Add selected to cart

☒ This item: [ErgoStar Ball End Hex L-Key Inch 13 Piece Set](#)

☒ [General Purpose Zipper Bag](#)

Details

L-Key's
.050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"
Corrosion protective Hard Chrome Finish
Long Arms are 15 to 20% longer
Wiha special chrome-vanadium-molybdenum tool steel
Ball End enables fastening and unfastening at an angle of up to 25°
Precision machine chamfered ends
No cut off burrs or impact distortions
Through hardened for best wear resistance

Holder
Downloaded from Arrow.com

Additional Info

SKU	66988
Weight (lbs)	2.5000
Packaging	Clamshell
Head Type	 ball end hex inch
Pieces In Set	13
L-Key Features	Ball End, ErgoStar Holder

Space-Saving ErgoStar Holder
For simplest removal of each individual L-Key
Fast and Secure
Rotate only one L-Key and all of them will move 90 degrees
With usefull hole for easy storage

PROP 65	yes
UPC	084705669885
UNSPSC	27111710
 Hex Inch Sizes	0.050" ~ 1.3mm 1/16" 5/64" 3/32" 7/64" 1/8" 9/64" 5/32" 3/16" 7/32" 1/4" 3/8"

Customers Also Bought



ErgoStar Ball End Hex L-Key Metric
9 Piece Set



ESD Safe Protorn 45° Precision
Flush Cut Cutters 18 AWG

Wiha Professional Quality Hand Tools



We produce Wiha products around the world under strict ISO quality standards. State of the art technology and special tool steels assure products consistent with our reputation for outstanding performance in demanding service, repair and production applications.

[Download Catalogs](#)
[Discounts and promotions](#)
[Filter and sort all Wiha hand tools](#)

Wiha Tools Canada Ltd. Since 2007

Wiha Canadian operations started bringing Wiha quality to professional tool users in 2007 with a warehouse located in Brampton, Ontario and sales office in the Greater Toronto Area.

[About Us](#)
[Privacy Policy](#)
[Terms and Conditions](#)
[Check the status of your order](#)
[Having technical issues with the website?](#)

Wiha Tools Canada Ltd.

A wholly owned Subsidiary of Willi Hahn Corporation

**Monday - Friday office hours 8AM - 5PM
CST USA**

No products are stocked at this location

394 Deerhurst Drive
Brampton, ON, L6T 5H9
Customer Service Email: info@wihatools.ca
Tel: **1(866) 494-0096**
Fax: 1(800) 494-7456
GST/HST number Business Number: 82851
5551 RT0001
[Shipping](#)
[Returns](#)
[Warranty Info](#)

