

Bazaar / Tools / Electrical Testers / USB Current Voltage Detector



USB Current Voltage Detector

SKU 114990067

Small size, simple and practical tool that can detect USB's voltage and current

OUT OF STOCK

This item is not available at the moment

[Get notified when it's back in stock](#)

Description

Small size, simple and practical tool that can detect USB's voltage and current. It doesn't need any external power, and plug and play. And it not only voltage and current detect, but also a USB hub. As a common USB detector, It has large detection range, 3.2v to 10v Voltage and 0A to 3A current.

Feature:

- Simple and practical
- Small size
- Convenient to carry
- No external power
- Plug and play

Specification:

- Min supply voltage: +3.2 V
- Max supply voltage: +10 V
- Measuring Range:DC 3.2-10V
- Operating temperature: -10 to 65° c
- Operating Humidity: 10 ~ 80% (no condensing)
- Working pressure: 80 ~ 106kPa
- Display Type:Digital Only
- Operating Temperature:-10 to 65° c
- Brand Name:DC Voltmeter Ammeter
- Accuracy Class:1% (± 2 digit)
- Dimensions:69 x 26 x 19mm
- Model Number:YB26VA 2in1 DC Volt Amp Meter
- USB extension cable:≥ 120mm
- Display:0.28"LED red
- Measuring rate:≥ 500mS / times

See More

Questions and Answers

Have a question about this? Ask people who own it.



Recommendations




Base Shield V2



LiPo Rider Pro




Grove - 4 pin Female Jumper to Grove...



Grove - RTC



ATX Breakout Board V1.1 Acrylic Case...



Grove - Moisture Sensor



Bus Pirate v3.6 universal serial...



CPT-C5 power converter 12V&24V...



Adjustable DC&DC Power Converter...



Grove - OLED Display 0.96"



ATX breakout board bench power supply

View History




315Mhz Wireless car key fob with key chain (batter...

ADD TO CART



Tiny Bread Board Kit

ADD TO CART




Hot Glue Sticks - 5pcs

ADD TO CART



Embedded Thermal Printer

ADD TO CART



Mini 125Khz RFID Module - Pre-Soldered Antenna (35...

ADD TO CART



1W Solar Panel 80X100



Grove - Universal 4 pin connector



JST 2 Pin power connector



Grove - Temperature&Humidity...



12mm Domed Push Button Pack



Grove - Starter Kit for Arduino



Grove - Relay



Aluminum Heatsink Kit for Raspberry Pi

Power converter 6 in 1 pack

POPULAR SEARCHES

PCB Manufacturing PCB Stencil Arduino XBee Arduino Shield Beaglebone Black Raspberry Pi Raspberry Pi Touchscreen Linkit Cubieboard Beaglebone Cape
FPGA Linkit ONE Crazyflie 2.0 Raspberry Pi 3 Model B RF Explorer DSO Nano v3 MediaTek X20 HiKey Board rplidar raspberry pi relay RPLIDAR A2



SHIPPING INFORMATION



KNOWLEDGE BASE



HELP CENTER

Sseed Info

Reach Us
Distributors
Designers
Careers
Site Map

Customer Service

Contact Us
Customer Support
Technical Support

Terms and Conditions

Order Information
Shipping Information
Payment Information
Warranty and Return
Terms of use
Privacy Policy

Stay Tuned

Subscribe to get the latest product releases, activities and tutorials from Sseed Studio.

>



Copyright © 2008-2017 Sseed Development Limited All rights reserved



Select Language ▼

Contact Support