



P	LTR	DESCRIPTION	DATE	DWN	APVD
	C3	REVISED PER ECN-26-388482	07MAY2026	NG	SVN






NOTES:

1. THIS FULLPROOF FIELD INSTALL KIT SHOULD BE USED WITH RUGGEDIZED CABLE AND RUGGED FAN-OUT CONSTRUCTION
NO 900 MICRON TERMINATIONS TO BE USED
2. CABLE DIAMETER RANGE: SEE TABLE
3. THE FLAMMABILITY RATING OF THE MATERIAL IS UL94-V0
4. THE MATERIAL IS HALOGEN FREE ACCORDING IEC 60754-2
5. EACH ASSEMBLY IS PACKED IN A PROTECTIVE SLEEVE
- GLAND SEAL AND NUT ARE SEPARATELY SEALED
6. AN INSTRUCTION SHEET IS PACKED WITH EACH FIELD INSTALL KIT
7. FITS TE CONNECTIVITY FULLAXS MINI BULKHEAD 2061981-X
- 8 2061973-4 INCLUDES THREE SEALS IN THE PACKAGING

TE Part Number	Cable Diameter
2061973-1	4.8±0.2 mm
2061973-2	5.0±0.2 mm
2061973-3	7.0±0.2 mm
8 2061973-4	4.8±0.2 mm
	6.0±0.2 mm
	7.0±0.2 mm

ASSEMBLED 2061973-X



PROTECTIVE SLEEVE PACKAGING
SCALE 4:5

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
	0 PLC ±0,5 1 PLC ±0,25 2 PLC ±0,03 3 PLC ±0,005 4 PLC ±0,0010 ANGLES ±1
MATERIAL	FINISH
-	-
-	-

3	FULLPROOF MINI FIELD INSTALL NUT FOR CABLE GLAND	1
2	FULLPROOF MINI FIELD INSTALL CABLE GLAND SEAL	1
1	FULLPROOF140 MINI FIELD INSTALL COUPLING	1
Item	Description	Qty

DWN R. COOLEN 10APR2015	TE Connectivity			
CHK M. SCHOLTEN 10APR2015				
APVD S. BORGAS 10APR2015	NAME FULLPROOF140 MINI FIELD INSTALL KIT			
PRODUCT SPEC 108-19489				
APPLICATION SPEC -				
WEIGHT -	SIZE A3	CAGE CODE -	DRAWING NO C-2061973	RESTRICTED TO -
CUSTOMER DRAWING	SCALE 1:2	SHEET 1 OF 1	REV C3	