
Downloaded from Arrow.com.

Thermofit® Molded Parts
Specification Control Drawing
Limited Distribution


Part Number : 202K163-25-02/225
Description : Boot, Straight With Lip

NOTES

1. All dimensions are in $\frac{\text{inches}}{\text{[millimeters]}}$
2. Dimensions appearing in table are as follows:
   a - As Supplied
   b - After Unrestricted Recovery
3. Coating is optional. As supplied dimensions appearing in table are for uncoated parts. When coating is added, entry diameters will be reduced by .06 max.
4. Eyelet Clip (000W212) is included with each part except those of -12. Clip is cadmium plated and olive drab color to Spec. QQ-P-416 Type II Class 3.



AS SUPPLIED



AFTER UNRESTRICTED RECOVERY

TABLE OF DIMENSIONS

PART NUMBER	H		J		P	R	S	T	JO	HW	JW
	Min a	Max b	Min a -12	Max b	±10% b	±10% b	±10% b	±10% b	±10% b	±20% b	Min b
202K163-25-02/225	1.69 [43.0]	1.11 [28.2]	1.69 [43.0]	.39 [9.9]	2.32 [59.0]	.83 [21.0]	.12 [3.0]	.07 [1.7]	.82 [21.0]	.08 [2.2]	.032 [0.81]

Raychem
RAYCHEM CORPORATION
300 CONSTITUTION DRIVE
MENLO PARK, CALIFORNIA 94025
(415) 361-6055

Revision : C
Date : 7/30/92

Part Number : 202K163-25-02/225
Description : Boot, Straight With Lip

Downloaded from Arrow.com.

Thermofit® Molded Parts
Specification Control Drawing
Limited Distribution

Part Number : 202K163-25-02/225
Description : Boot, Straight with Lip

COMPATABILITY CHART					
MATERIAL DASH NO.	MATERIAL DESCRIPTION	RT SPEC	COATING SLASH NO.	COATING S NO.	COATING DESCRIPTION
-25	Elastomer, Fluid Resistant	RT-1325	/225	S-1206	Adhesive

ORDERING INFORMATION

202K163 -25 -02 /225

Base part number

Material dash number
(See Compatability Chart)

Modification number
(If necessary, see front of scd binder for a complete list)

Adhesive slash number
(If necessary, see Compatability Chart)

THIS DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE: CONSULT YOUR NEAREST FIELD REPRESENTATIVE FOR CURRENT REVISION

Raychem
RAYCHEM CORPORATION
300 CONSTITUTION DRIVE
MENLO PARK, CALIFORNIA 94025
(415) 361-6055

Revision : C
Date : 7/30/92

Part Number : 202K163-25-02/225
Description : Boot, Straight With Lip

CAD FILE MP9235