



Part Number : [639046800](#)
Product Description : FineAdjust Applicator for 2.00mm Pitch Wire-to-Board Crimp Terminal, 30-24 AWG, Insulation OD 0.90-1.10mm
Series Number : 207127
Status : Active
Product Category : Applicators and Crimp Modules

Documents & Resources

Tooling Specifications

[639046800-000.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Applicators and Crimp Modules
Series	207127
Description	FineAdjust Applicator for 2.00mm Pitch Wire-to-Board Crimp Terminal, 30-24 AWG, Insulation OD 0.90-1.10mm
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Automatic, Semi-Automatic
More Detailed Tech Information	toolingsupport@molex.com
Product Name	FineAdjust
Tool Type	Applicator
UPC	193264021604
Warranty Disclaimer	<p>CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.</p>

Physical

Net Weight	1.000/g
------------	---------

Applicable Parts

Description	Part Number
2.00mm Pitch, Micro-Latch Female Crimp Terminal, Tin (Sn) Plating, 30-24 AWG, Reel	<u>502128000</u>
2.00mm Pitch, Milli-Grid Female Crimp Terminal, 0.38µm Select Gold, Reel, Lead free	<u>503948051</u>
2.00mm Pitch, Milli-Grid Female Crimp Terminal, 0.76µm Select Gold, Reel, Lead-Free	<u>503948052</u>
2.00mm Pitch, Milli-Grid Female Crimp Terminal, Gold (Au) Flash, Reel, Lead free	<u>503948054</u>
2.00mm Pitch, Milli-Grid Female Crimp Terminal, Matte Tin Plating, Reel, Lead free	<u>503948055</u>
2.00mm Pitch, Milli-Grid Female Crimp Terminal, Unplated, Reel, Lead-Free	<u>503948999</u>
2.00mm Pitch, Micro-Latch Female Crimp Terminal, Gold (Au) Plating, 28-24 AWG, Reel	<u>593548081</u>

This document was generated on Sep 25, 2025