




Part Number : [2078450004](#)

Product Description : KK Plus 250 Terminal Position Assurance (TPA) Retainer, 4 Circuits, Natural

Series Number : 207845

Status : Active

Product Category : Connector Accessories



Documents and Resources

Drawings

[2078450004_sd.pdf](#)

[2078450000-PK-000.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[2079020001-AS-000.pdf](#)

[2079020001-PS-000.pdf](#)

[2079020001-PS-CH-000.pdf](#)

[2079020001-PS-ES-000.pdf](#)


[2079020001-PS-JP-000.pdf](#)

[2079020001-PS-SK-000.pdf](#)

[2079020000-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21

REACH SVHC	Contains 1,1'-(Ethane-1,2-diyl)bis[pentabromobenzene] per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Accessories
Series	207845
Description	KK Plus 250 Terminal Position Assurance (TPA) Retainer, 4 Circuits, Natural
Component Type	Terminal Position Assurance (TPA)
Product Name	KK Plus
UPC	191130124022

Agency

CSA	152514
-----	--------

Physical

Circuits (Loaded)	4
-------------------	---

Circuits (maximum)	4
Color - Resin	Natural
Flammability	94V-0
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	0.074/g
Number of Rows	1
Packaging Type	Bag
Temperature Range - Operating	-40° to +105°C

Mates With / Use With

Use with Part(s)

Description	Part Number
KK Plus 250 Receptacle Housing, 2.50mm Pitch, Single Row, 4 Circuits, UL 94V-0, Black, Glow-Wire Capable	<u>2078410004</u>

This document was generated on Apr 20, 2026