



Part Number : [2169465011](#)

Product Description : Ultra-Fit Crimp Terminal, Male, 0.38µm Gold (Au) Plating, 16-18 AWG

Series Number : 216946

Status : Active

Product Category : Crimp Terminals

Documents & Resources

Drawings

[Drawing 2169465011_sd.pdf](#)


Specifications

[Application Specification 1723230003-000.pdf](#)

[Test Summary 2169460001-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Crimp Terminals
Series	216946
Description	Ultra-Fit Crimp Terminal, Male, 0.38µm Gold (Au) Plating, 16-18 AWG
Application	Power, Wire-to-Wire
Comments	See Product Specification for maximum current rating by circuit size and wire AWG
Product Family	Ultra-Fit Power Connectors
Product Name	Ultra-Fit
UPC	195842154254

Agency

UL	E29179
----	--------

Electrical

Voltage - Maximum	600V AC (RMS)/DC
-------------------	------------------

Physical

Durability (mating cycles max)	200
Flammability	94V-0
Gender	Male
Material - Metal	Phosphor Bronze Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Matte Tin
Net Weight	0.160/g
Packaging Type	Reel
Plating min - Mating	0.380µm
Plating min - Termination	2.500µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.70-2.00mm
Wire Size (AWG)	16, 18

Wire Size mm ²	N/A
---------------------------	-----

Use with Part(s)

Description	Part Number
Ultra-Fit Single Row Plug Housings	<u>202569</u>
Ultra-Fit Dual Row Plug Housings	<u>216945</u>

Application Tooling

Global

Description	Part Number
Extraction Tool for Ultra-Fit Plug Terminals, 16-18 AWG and 20-22 AWG Wires	<u>2002221700</u>
FineAdjust Applicator for Ultra-Fit Tangless Male Crimp Terminals, 16-18 AWG, UL1061 Wire	<u>2037024300</u>
Hand Crimp Tool for Ultra-Fit Tangless Male and Female Terminals, 16-18 AWG (UL 1061) Wire	<u>2133096200</u>

This document was generated on Jul 15, 2024