


1-1985847-5 Product Details

[Share](#) [Print](#) [Email](#)


1-1985847-5

TE Internal Number: 1-1985847-5

 [Active](#)

Fiber Optic Cable Assemblies

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Cable Assembly
- FOKIT ODC Fiber Optic Cable Connector Type, LC Fiber Optic Cable Connector Type
- Fiber Type = 50/125 Micron
- Cable Assembly Type = FOKIT ODC to 2 LC Duplex
- Multimode

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

 [Add to My Part List](#)  [Request Sample](#)  [Find Similar Products](#)  [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [FIBER OPTIC ODC LEAD 4 FOLD PLUG - 2x LC DUPLEX MULT...](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Cable Assembly
- Fiber Optic Cable Connector Type = FOKIT ODC, LC
- Cable Assembly Type = FOKIT ODC to 2 LC Duplex
- Cable Type = FOCAB ODC

Termination Features:

- [Fiber Type \(Micron\)](#) = 50/125
- [Mode](#) = Multimode

Body Features:

- Cable Diameter (mm [in]) = 5.50 [.216]
- Number of Fibers = 4
- Cable Color = Black
- Length (M [ft]) = 150.00 [492.126]
- Connector Color = Beige, Black
- Protective Cap = With

Contact Features:

- Boot Body Style - Left = Standard
- Boot Color - Left = Black
- Boot Body Style - Right = Standard
- Boot Color - Right = Beige
- Fibre Channel = No

Configuration Features:

- [Cable Buffering](#) = Tight Buffered
- Connector(s) Exit Angle to Connector(s) Exit Angle = 180° to 180°

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Other:

- Brand = Tyco Electronics

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

