

Short Slope Console (1599 Series)

Plastic



FEATURES (Fire Retardant - ABS Version)

- Attractively styled and ergonomically designed, molded in flame retardant ABS grey or black plastic (material carries a UL flammability rating of 94V-0).
- Rear of units contain one or two (depending on width), removable panels for easy modifications (see our website).
- Two piece lap joint construction provides protection against access of dust and splashing water.
- Designed to meet IP54.
- P.C. board card bosses are molded in for easy installation (see our website).
- Accessory screws for mounting P.C. boards into standoffs P/N **1593ATS50** (qty. 50), P/N **1593ATS100** (qty. 100).
- Base is secured with machine screws into brass bushings for repetitive assembly and disassembly.

Part Number		Rear Panel	P.C. Card Bosses		Units	Dimensions			
Black	Grey		Base	Top		Width	Length	Depth (Rear)	Depth (Front)
1599ETSBK	1599ETSGY	1	6	-	inch mm	3.37 85.5	6.69 170	1.34 34.1	0.73 18.6
1599HTSBK	1599HTSGY	2	6	-	inch mm	4.33 110	8.66 220	1.57 40	0.75 19
1599KTSBK	1599KTSGY	2	8	8	inch mm	5.51 140	8.66 220	1.83 46.5	0.82 20.7

FEATURES (Polystyrene Version)

- Same features as above except molded in economical polystyrene.
- Polystyrene version uses self-tapping screws. Perfect where economy is important and where repetitive assembly and disassembly of lid is not vital.

Part Number	Color	Rear Panel	P.C. Card Bosses		Units	Dimensions			
			Base	Top		Width	Length	Depth (Rear)	Depth (Front)
1599ESTSGY	Grey	1	6	-	inch mm	3.37 85.5	6.69 170	1.34 34.1	0.73 18.6
1599HSTSGY	Grey	2	6	-	inch mm	4.33 110	8.66 220	1.57 40	0.75 19
1599KSTSGY	Grey	2	8	8	inch mm	5.51 140	8.66 220	1.83 46.5	0.82 20.7

Long Slope Console (1599 Series)



Plastic

FEATURES (Fire Retardant - ABS Version)

- Attractively styled and ergonomically designed, molded in flame retardant ABS grey or black plastic (material carries a UL flammability rating of 94V-0).
- Rear of unit contains one removable panel for easy modifications (see our website).
- Two piece lap joint construction provides protection against access of dust and splashing water.
- Designed to meet IP54.
- P.C. board card bosses are molded in for easy installation (see our website).
- Accessory screws for mounting P.C. boards into standoffs P/N **1593ATS50** (qty. 50), P/N **1593ATS100** (qty. 100).
- Base is secured with machine screws into brass bushings for repetitive assembly and disassembly.

Part Number		Battery Door	Rear Panel	P.C. Card Bosses		Units	Dimensions			
Black	Grey			Base	Top		Width	Length	Depth (Rear)	Depth (Front)
1599KTLBK	1599KTLGY	-	1	8	8	inch mm	5.50 140	8.66 220	1.60 40.5	0.71 18
1599KTLBKBAT	1599KTLGYBAT	Yes	1	8	8	inch mm	5.50 140	8.66 220	1.60 40.5	0.71 18

FEATURES (Polystyrene Version)

- Same features as above except molded in economical polystyrene.
- Polystyrene version uses self-tapping screws. Perfect where economy is important and where repetitive assembly and disassembly of lid is not vital.

Part Number	Color	Battery Door	Rear Panel	P.C. Card Bosses		Units	Dimensions			
				Base	Top		Width	Length	Depth (Rear)	Depth (Front)
1599KSTLGY	Grey	-	1	8	8	inch mm	5.50 140	8.66 220	1.60 40.5	0.71 18
1599KSTLGYBAT	Grey	Yes	1	8	8	inch mm	5.50 140	8.66 220	1.60 40.5	0.71 18



CANADA

Guelph, Ontario (519) 822-2960
St. Laurent, Quebec (514) 343-9010

USA

Cheektowaga, NY (716) 651-0086



EUROPE

Basingstoke, UK +44 1256 812812

AUSTRALASIA

Queenstown, SA, Australia +61 8 8240 2244

Accessories (1599 Series)

ACCESSORIES

Plastic



Replacement Screws for ABS

Machine screw, used in flame retardant ABS 1599B series (ie...with brass inserts).

M3 - 0.5 x 20 mm

1594MS100 - Package of 100

Machine screw, used in flame retardant ABS 1599E, H & K series (ie...with brass inserts).

M3 - 0.5 x 10 mm

1591MS100 - Package of 100



Replacement Screws for Polystyrene

Self-tapping type, used in polystyrene 1599BS series (ie...no brass inserts).

4 x 3/4"

1599BTS100 - Package of 100

Self-tapping type, used in polystyrene 1599ES, HS & KS series (ie...no brass inserts). # 4 x 5/8"

1598TS100 - Package of 100

Battery Holder Kits

- Designed for our battery door enclosures.
- Kits include all the parts required to install the battery or batteries.
- Kit includes the battery holder, wires, divider and foam anti-rattle pad.

Part Number	Battery holder kit for:	Fits Battery Door Enclosure Size:
BH1AAWKIT	1 AA Cell	B, E, H & K
BH2AAWKIT	2 AA Cells	B, E, H & K
BH1AAAWKIT	1 AAA Cell	B, E, H & K
BH2AAAWKIT	2 AAA Cells	B, E, H & K
BH3AAAWKIT	3 AAA Cells	E, H & K
BH4AAAWKIT	4 AAA Cells	E, H & K
BS61KIT	1 - 9V Cell	B, E, H & K

Nylon screws for electrical insulation and strength...



High strength nylon clip for belt or pocket...

Belt or Pocket Clip (for hand held)

Molded from tough nylon, includes 2 nylon screws and mounting template.

Black - **1599CLIP**

Grey - **1599CLIPGY**

P.C. Board Mounting Screws

Self-tapping type, used for bosses in the 1599 series for P.C. board installation. # 4 x 1/4" (6.4 mm)

1593ATS50 - Package of 50

1593ATS100 - Package of 100



Battery Dividers (for hand held)

Grey ABS plastic panel barriers which insert vertically into the P.C. card guides of the 1599B series.

1599BD5 - Package of 5

1599BD100 - Package of 100

Grey ABS plastic panel barriers which insert vertically into the P.C. card guides of the 1599E series.

1599ED5 - Package of 5

1599ED100 - Package of 100

Grey ABS plastic panel barriers which insert vertically into the P.C. card guides of the 1599H series.

1599HD5 - Package of 5

1599HD100 - Package of 100

