Part Number : 936010632
Product Description : Heavy-Duty Standard (STD) Single Lever Hood, Polyamide, with 2 Pegs, Top Entry, Size 3A «21x21», Pg11 Thread, Grey White
Series Number : 93601
Status : Active
Product Category : Heavy-Duty Connectors
Engineering Part Number : 7803.6207.0



Documents and Resources

Drawings

936010632_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

Status	Active
Category	Heavy Duty Connectors
Series	93601
Description	Heavy-Duty Standard (STD) Single Lever Hood, Polyamide, with 2 Pegs, Top Entry, Size 3A «21x21», Pg11 Thread, Grey White
Comments	IP67 with screw gasket.
Component Type	Single Lever Hood
IP Rating	IP66
Product Name	Heavy-Duty Connectors
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	STD
UPC	887191838892

Agency

CSA	256883
UL	E249674

Electrical

Voltage - Maximum	230V / 400V

Physical

Component Size	3A «21x21»
Entry Location	Top
Hood Color	Grey White RAL 9002

Downloaded from Arrow.com.

Lock to Mating Part	Yes
Material - Hood	Polyamide
Material - Peg	Polyamide
Net Weight	12.300/g
Number of Pegs	2
Packaging Type	Bag
Thread Size	Pg11
Thread Type	(Pg)

Mates With / Use With

Use with Part(s)

Description	Part Number
Use With	Size 3A «21x21» S-A, S-D, and S-Q Inserts

Downloaded from Arrow.com.