
CE PLAN EST UN DOCUMENT CONTROLE PAR TYCO ELECTRONICS CORPORATION.
IL EST SUSCEPTIBLE D'ETRE REVISE. POUR OBTENIR LA DERNIERE REVISION,
CONTACTER LE SERVICE TECHNIQUE DE TYCO ELECTRONICS SIMEL SAS
21220 GEVREY-CHAMBERTIN, FRANCE

THIS DRAWING IS A CONTROLLED DOCUMENT.


LOC	DIST
FH	00


REVISIONS

P	LTR REV	DESCRIPTION MODIFICATIONS	DATE	DWN DESS.	APVD APP.
	F	MISE A JOURS / AJOUT NOTA	07DEC2009	BG	GP
	G	ECR-11-018538	07SEP2011	LP	NA




COUPE A-A





Ces produits répondent à la norme NFC 20-130.
These products are NFC 20-130 compliant.



(L)	C	B	ØA	DESCRIPTION	PART NUMBER
39	7	15	6,4	XCT 35-6	710027-1
46	11	17	8,3	XCT 35-8	710027-2
46	11	17	10,3	XCT 35-10	710036-3
46	11	17	12,8	XCT 35-12	710036-4

1 - MATERIAL = TINNED COPPER

2 - Marking in depth: logo-section-hole-Made in France +

3 - CABLE SECTION = 2AWG or 35mm2

4 - GROOVE E35Cu OR DIE (Punch 17P50+ Die 17M35)

TOLERANCES UNLESS OTHERWISE SPECIFIED -
TOLERANCES NON SPECIFIEES: -

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
TOLERANCES NON SPECIFIEES (SUIV NB DE DECIMALES):
0 PLC/DEC: ±0
1 PLC/DEC: ±0
2 PLC/DEC: ±0
3 PLC/DEC: ±0
4 PLC/DEC: ±0
ANGLES ±-

DWN/DESSINE D.LEGUY 15DEC00
CHK/VERIFIE E.DEREY -
APVD/APPROUVE N.ALMEIDA -
PRODUCT SPEC SPEC. PRODUIT -
APPLICATION SPEC SPEC. APPLICATION -
WEIGHT MASSE APPROX.

MATERIAL MATIERE: CUIVRE
FINISH FINITION: ETAME

TE Connectivity

NAME TITRE: XCT 35-..

SIZE FORMAT: A4
CAGE CODE: 00779
DRAWING NO No PLAN: C-710027
RESTRICTED TO RESERVE A: -

CUSTOMER DRAWING /PLAN CLIENT UNIQUEMENT POUR REFERENCE
SCALE ECHELLE: - / -
SHEET FEUILLE: 1 OF DE: 1
REV: G

1469-35 (3/11)

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
DIFFUSION RESTREINTE - LIBRE A LA DIFFUSION
© COPYRIGHT 20 ALL RIGHTS RESERVED.
TOUS DROITS RESERVES.

Downloaded from Arrow.com.