
MICRO SWITCH
FREEPORT ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

SWITCH—BASIC

CATALOG LISTING
BZ-1RW8255051T-S

5



NOTES
⚠1 – MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX DIA ON 1.000±.002 CENTERS
2 – SEALED CONSTRUCTION PROVIDES SPLASH RESISTANCE

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION

CHARACTERISTICS

OPERATING FORCE – – – – – 3 OZ MAX
RELEASE FORCE – – – – – – – 3/4 OZ MIN
DIFFERENTIAL TRAVEL – – – .008–.020
OVERTRAVEL – – – – – – – – – .156 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

L103
15A 125, 250 OR 480 VAC
1/8 HP 125 VAC, 1/4 HP 250 VAC

L288
L299
L306
16A 250V ~ T85 5E4

SCALE FULL
DO NOT SCALE PRINT

TOLERANCES
APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE ±

	DIM. mm	TOL. mm/in	DIM. in	TOL. mm/in
NO PLACES	X	1/.04		
ONE PLACE	X,X	0.4/.016	X.X	0.8/.03
TWO PLACES	X,XX	0.15/.006	X.XX	0.38/.015
THREE PLACES			X.XXX	0.13/.005
ANGLES				

DESIGN UNITS: SI METRIC ☐ US CUSTOMARY ■

WEIGHT .079 LB

REVISIONS

A	C067209	J A P 2 MAY 90
B	CO-69351-D	JWB 18 JUL 91
C	CO-75204B	JWB 1 FEB 94
D	C093346	D L T 4 SEP 98

ISSUE 5 | DRAWING NUMBER M BZ-1RW8255051T-S PAGE 1 OF 1 | RELEASE NO. PR-8526 | REPLACES X70639-BZ

J A P 16 MAR 80 DRAWN | C E B 8 MAR 80 CHECK | CHECK | CHECK | CHECK

FORMTEK F0-52848-A

Downloaded from Arrow.com.