



**Part Number :** [50579202](#)

**Product Description :** SL Crimp Housing, Single Row, Version C, Front Ribs, 2 Circuits, Black

**Series Number :** 70066

**Status :** Active

**Product Category :** Connector Housings

**Engineering Part Number :** 70066-0071



---

## Documents and Resources

### Drawings

[050579202\\_sd.pdf](#)

[PK-70066-100-001.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

### Specifications

[PS-70058-001.pdf](#)

[PS-70400-001.pdf](#)


[PS-71851-001.pdf](#)

[TS-70058-001-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

## Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

## Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Connector Housings
Series	70066
Description	SL Crimp Housing, Single Row, Version C, Front Ribs, 2 Circuits, Black
Application	Signal, Wire-to-Board
Comments	Version C
Product Name	SL
UPC	800753757202

### Agency

CSA	LR19980
UL	E29179

### Physical

Circuits (maximum)	2
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No

Keying to Mating Part	Yes
Lock to Mating Part	No
Material - Resin	Polyester
Net Weight	0.016/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm
Stackable	No
Temperature Range - Operating	-40° to +105°C

### Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
SL Vertical Single Row Headers	<a href="#">70541</a>
SL Vertical Single Row Headers	<a href="#">70543</a>
SL Vertical Single Row Headers	<a href="#">70545</a>
SL Right-Angle Single Row Headers	<a href="#">70551</a>
SL Right-Angle, Single Row, Low Profile Headers	<a href="#">70553</a>
SL Right-Angle Single Row Headers	<a href="#">70555</a>
SL Right-Angle, Single Row, Low Profile, Surface Mount Headers	<a href="#">70634</a>
SL Vertical, Single Row, Surface Mount Headers	<a href="#">74099</a>

### Use with Part(s)

Description	Part Number
SL Female Terminals	<a href="#">70058</a>
SL Female Terminals	<a href="#">71851</a>

---

This document was generated on May 06, 2026