

# Product data sheet

Specifications



## APC NetShelter SX, Server Rack Enclosure, Colocation, 42U, Black, 1991H x 600W x 1070D mm

AR3200

### Overview

|              |                                                                                                                                                                                                                             |
|--------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Presentation | Two compartment enclosure for colocation facilities with customers requiring a minimal amount of rack space. This multi-tenant, security enhanced enclosure is provided with a compact width to optimize data center space. |
| Lead time    | Usually in Stock                                                                                                                                                                                                            |

### Main

|                           |                                                                                                                                                                                                                              |
|---------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Product or component type | Rack enclosure                                                                                                                                                                                                               |
| Number of rack unit       | 42U                                                                                                                                                                                                                          |
| Provided equipment        | 3-digit combination style handles<br>Adjustable vertical mounting rails<br>Baying hardware<br>Documentation CD<br>Door key<br>Installation guide<br>Leveling feet<br>Pre-installed casters<br>Rack mounting hardware<br>Roof |

### Physical

|                            |                                                                                                                                   |
|----------------------------|-----------------------------------------------------------------------------------------------------------------------------------|
| Height                     | 199.1 cm                                                                                                                          |
| Width                      | 60 cm                                                                                                                             |
| Depth                      | 107 cm                                                                                                                            |
| Net weight                 | 140.7 kg                                                                                                                          |
| Colour                     | Black                                                                                                                             |
| Mounting preference        | No preference                                                                                                                     |
| Mounting mode              | Not rack-mountable                                                                                                                |
| Maximum mounting depth     | 94.49 cm                                                                                                                          |
| Rack width                 | 19"                                                                                                                               |
| Marking                    | 14 gauge EIA mounting rail<br>16 gauge front door<br>16 gauge post<br>18 gauge rear door<br>18 gauge roof<br>18 gauge side panels |
| Permanent permissible load | 1020.6 kg dynamic<br>1701.0 kg static                                                                                             |

### Conformance

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|           |                                   |
|-----------|-----------------------------------|
| Standards | UL 2416<br>UL 60950-1<br>EIA-310E |
|-----------|-----------------------------------|

## Packing Units

|                              |           |
|------------------------------|-----------|
| Unit Type of Package 1       | PCE       |
| Number of Units in Package 1 | 1         |
| Package 1 Height             | 211.7 cm  |
| Package 1 Width              | 74.6 cm   |
| Package 1 Length             | 115.6 cm  |
| Package 1 Weight             | 168.35 kg |

## Contractual warranty

|          |                          |
|----------|--------------------------|
| Warranty | 5 year repair or replace |
|----------|--------------------------|

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

| Environmental footprint          |     |
|----------------------------------|-----|
| Total lifecycle Carbon footprint | 511 |

Use Better

| Materials and Substances               |                                                            |
|----------------------------------------|------------------------------------------------------------|
| Packaging made with recycled cardboard | No                                                         |
| Packaging without single use plastic   | No                                                         |
| <a href="#">EU RoHS Directive</a>      | Pro-active compliance (Product out of EU RoHS legal scope) |
| REACH Regulation                       | <a href="#">REACH Declaration</a>                          |

Use Again

| Repack and remanufacture        |                                                                                                                                                                                                                 |
|---------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| End of life manual availability | <a href="#">End of Life Information</a>                                                                                                                                                                         |
| Take-back                       | Yes                                                                                                                                                                                                             |
| WEEE Label                      |  The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |

Image of product / Alternate images

Alternative

---







