


Color: ■ green-yellow



Dimensions in mm

| Technical data | |
|----------------------------|---|
| Total number of potentials | 1 |

| Electrical data | |
|-----------------|------|
| Rated current | 20 A |
| Test voltage | 42 V |

| Connection data | |
|-------------------------|------------------------------------|
| Connection technology | CAGE CLAMP® |
| Strip length | 9 ... 11 mm / 0.35 ... 0.43 inches |
| Clamping units | 1 |
| Solid conductor | 0.08 ... 2.5 mm² / 28 ... 14 AWG |
| Fine-stranded conductor | 0.08 ... 2.5 mm² / 28 ... 14 AWG |

| Physical data | |
|---------------|----------------------|
| Width | 8 mm / 0.315 inches |
| Height | 15 mm / 0.591 inches |
| Depth | 40 mm / 1.575 inches |

| Material data | |
|---------------|--------------|
| Color | green-yellow |
| Fire load | 0.04 MJ |
| Weight | 3.9 g |



| Commercial data | | |
|-----------------------|--------------------------------|--|
| Product Group | 2 (Terminal Block Accessories) | |
| PU (SPU) | 50 pcs | |
| Packaging type | Box | |
| Country of origin | DE | |
| GTIN | 4045454293567 | |
| Customs tariff number | 85366990990 | |

| Product classification | | |
|------------------------|----------------------|--|
| UNSPSC | 39121421 | |
| eCl@ss 10.0 | 27-44-03-13 | |
| eCl@ss 9.0 | 27-44-03-13 | |
| ETIM 9.0 | EC002255 | |
| ETIM 8.0 | EC002255 | |
| ECCN | NO US CLASSIFICATION | |

| Environmental Product Compliance | | |
|---|--------------------------------------|--|
| CAS-No. | 7439-92-1 | |
| REACH Candidate List Substance | Lead | |
| RoHS Compliance Status | Compliant,With Exemption | |
| RoHS Exemption | 6(c) | |
| SCIP notification number (Austria) | 11a03ff5-a36f-43da-b613-56f9cc3f0f73 | |
| SCIP notification number (Belgium) | b76949c6-e6eb-48b3-8a4f-d3e40bb5bbf3 | |
| SCIP notification number (Bulgaria) | ba74eb32-6f43-4bff-bbdd-110f2dd35b0c | |
| SCIP notification number (Czech Republic) | b7e4d258-b776-4d4c-873e-0b1622a09379 | |
| SCIP notification number (Denmark) | 374f27a2-7a2f-489b-b3d3-db34ca1eeee9 | |
| SCIP notification number (Finland) | fba41022-f292-4a5d-929b-4be4bf903756 | |
| SCIP notification number (France) | a2e81971-2a70-4c24-8d8c-d887d2a26d87 | |
| SCIP notification number (Germany) | 534e3015-7658-4225-9766-10ffea125f7f | |
| SCIP notification number (Hungary) | 49d347b9-f772-482a-9f27-3f50e55ac4b7 | |
| SCIP notification number (Italy) | cf5684cb-e759-4fd2-a561-851d016e9e8f | |
| SCIP notification number (Netherlands) | e676c47b-5ec8-4fa4-b85c-ba063cf9c9c3 | |
| SCIP notification number (Poland) | 3fed0584-489d-4db5-ad3b-455b0e19a745 | |
| SCIP notification number (Romania) | 789bcf42-8b74-4a01-95ad-e85601b1f323 | |
| SCIP notification number (Sweden) | a7d62418-380b-4e56-a926-5857023c5344 | |

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 215-911

↓

Documentation

| Bid Text | | | |
|----------|------------|-----------------|-------------------|
| 215-911 | 19.02.2019 | xml 3.02 KB | ↓ |
| 215-911 | 19.09.2017 | doc 25.50 KB | ↓ |

CAD/CAE-Data

| CAD data |
|----------------------|
| 2D/3D Models 215-911 |

[↓](#)

| CAE data |
|------------------------------|
| EPLAN Data Portal 215-911 |


[↓](#)

| |
|---------------------------|
| WSCAD Universe 215-911 |
|---------------------------|

[↓](#)


Installation Notes

Conductor termination



Conductor termination: Press button fully, insert stripped conductor into square entry and release.

Testing



Testing via banana plug.
Picture shows a test plug adapter (Item No. 209-170).