

2134059-1 Product Details

 Share  Print  Email



 Active

 View 3D PDF

Dynamic Series Connectors

DYNAMIC D7300 SOCKET HSG ASSY RVS 4P XX

2134059-1 

TE Internal Number: 2134059-1

Product Highlights [View All](#)

- Dynamic Series Product Line
- D-7300 Series
- Series No. = 7000
- Wire-to-Wire
- Applies To Panel

Pricing & Availability 

Request Sample 

Add to My Part List 

Buy Product through
Distributor 

 Feedback

Documents

Features

Compliance

Please Note:

Use the Product Drawing for all design activity

Product Type Features

Product Line	Dynamic Series
Product Type	Connector
Connector Type	Housing
Sealed	No

Mechanical Attachment

Panel Mount Retention	With
Panel Mount Retention Type	Screw Mount

Electrical Characteristics

Operating Voltage Reference	AC/DC
Operating Voltage (VAC)	630
Operating Voltage (VDC)	630

Body Features

Row-to-Row Spacing (mm [in])	16.00 [0.6299]
Mating Retention	Without

Contact Features

Contact Type	Socket
Contact Layout	Dual Row
Multiple Contact Types	Without

Housing Features

Connector Style	Receptacle
Centerline (mm [in])	16.00 [0.630]
Housing Material 	Thermoplastic
Housing Color	Black
Mating Alignment	With
Mating Alignment Type	Keyed

Configuration Features

Number of Positions 	4
Number of Rows 	2

Industry Standards

RoHS/ELV Compliance 	RoHS compliant, ELV compliant
Lead Free Solder Processes 	Not relevant for lead free process
RoHS/ELV Compliance History	Always was RoHS compliant
UL Flammability Rating	UL 94V-0 

Identification Marking

Keying 	XX
--	----

Environmental

Operating Temperature (°C [°F])	-55 - +105 [-67 - +221]
---------------------------------	-------------------------

Conditions for Usage

Applies To 	Panel
For Use With	Plug Housing

Operation/Application

Application Use	Wire-to-Wire
-----------------	--------------

Packaging Features

Packaging Method	Tray/Box
Packaging Quantity	12

Other

Series	D-7300
Series No.	7000
Brand	TE Connectivity

Related Products

Not quite the product
you're looking for?

[Find Similar Products](#)

[View Part in Product
Feature Selector](#)

[Check for Tooling](#)

Corporate Information

About TE
Investors
News Room
Supplier Portal
Careers
Terms & Conditions
Privacy Policy
Global Accessibility Statement

Quick Links

Distributor Inventory
Product Cross Reference
Documents & Drawings
Product Compliance Support Center
Site Map

Customer Support

Email or Chat With Us
Find a Phone Number
Knowledge Base
Manage Your Account

Keep Me Informed

