



Menu

HOME / SUPERMICRO 740W 1U REDUNDANT POWER SUPPLY (PWS-741P-1R)

Feedback

IN STOCK

\$182.70

Buy 10 \$175.16/each

Buy 100 \$167.62/each

Buy 1000 \$160.08/each

• PMBus 1.2 Support for Remote Management

• Flexible Redundancy Control

• 80 Plus Platinum

• Supermicro Certified

Qty: 1

ADD TO CART

Add to Wishlist

Add to Compare

More Views

PLEASE ENTER SKU# TO CHECK VALIDATION STATUS

System

Chassis

SKU #:

Please enter your server SKU

VALIDATION STATUS

CLEAR

i

Description

[Detailed Specification](#)

[Prop 65 Warning](#)

Description

The Supermicro PWS-741P-1R is an 80 Plus Platinum level redundant power supply capable of supplying output power at 94% efficiency. Enjoy the simplicity of active power factor correction (PFC) and correct AC input for a full range of voltages. Features a card edge connector for connection with the backplane.

<https://store.supermicro.com/740w-1u-pws-741p-1r.html>

Downloaded from [Arrow.com](#)

1/3

of compatible Supermicro 1U systems. This power supply is designed to not only provide you reliable power to your Supermicro server but also protects it from over voltage, over current and short circuiting via protective circuitry embedded into the unit. Rest easy knowing your hardware will be up and running with a mean-time between failure (MTBF) of greater than 200,000 hours and an LED indicator to keep you informed on normal/abnormal conditions for your PSU. This power supply is redundant to safe-guard your system from power failure and allows for hot-swap replacement to eliminate system downtime. All materials contained comply with RoHS requirements and is certified by Supermicro.

Detailed Specification

TOTAL POWER OUTPUT	740W
TYPE	Module
TYPE OF POWER SUPPLY	Power Supply
FORM FACTOR	1U
DIMENSION (W X H X L)	76 x 40.4 x 336mm
5V	N/A
+12V	61.7A
+3.3V	N/A
5V STANDBY	4A
INPUT VOLTAGE RANGE	100-240Vac
INPUT FREQUENCY RANGE	50-60Hz
INPUT CURRENT RANGE	10-3.5A
OUTPUT TYPE	Gold Finger (19 Pair Connector)
8PIN / 4PIN (12V) CONNECTOR	N/A
PFC	Yes
PMBUS	Yes
ENERGY EFFICIENCY	94% Peak
80 PLUS CERTIFICATION	80 Plus Platinum
WARRANTY	1 year warranty
PRODUCT ENVIRONMENTAL COMPLIANCE	RoHS and REACH compliant, details available upon request

Prop 65 Warning

This product can expose you to chemicals including lead, known to the State of California cause cancer and birth defects or other reproductive harm. For more information, go to



COMPANY

- ABOUT US
- CONTACT US
- CONDITION OF USE
- PRIVACY POLICY

QUICK LINKS

- FAQ

ACCOUNT

- MY ACCOUNT
- RETURN POLICY
- WARRANTY POLICY

SIGN UP FOR SPECIAL OFFERS

SIGN UP

CONNECT WITH US

- FACEBOOK
- TWITTER
- YOUTUBE
- LINKEDIN
- GOOGLE+

