

P/N: T910891ACC

Copyright

© 2024, FLIR Systems, Inc.

All rights reserved worldwide. Names and marks appearing herein are either registered trademarks or trademarks of FLIR Systems and/or its subsidiaries. All other trademarks, trade names or company names referenced herein are used for identification only and are the property of their respective owners.

Document identity

Publ. No.: T910891ACC

Release: AA

Commit: 96121

Language: en-US

Modified: 2024-02-12

Formatted: 2024-02-12

Website

<http://www.flir.com>

Customer support

<http://support.flir.com>

Disclaimer

Specifications subject to change without further notice. Camera models and accessories subject to regional market considerations. License procedures may apply. Products described herein may be subject to US Export Regulations. Please refer to exportquestions@flir.com with any questions.



General description	
This cable is used to connect the infrared camera with an external display.	
Physical data	
Weight	137 g (4.8 oz.)
Cable length	1.5 m (4.9 ft.)
Connector	HDMI type C to HDMI type A
Shipping information	
Packaging, type	Cardboard box
Packaging, weight	0.219 kg (0.48 lb.)
Packaging, size	161 × 134 × 67 mm (6.3 × 5.3 × 2.6 in.)
EAN-13	7332558006306
UPC-12	845188006655
Country of origin	China

Compatible with the following products:

- 10301-0102; FLIR G615 20°
- 10401-0101; FLIR Gx320 14.5°
- 10401-0102; FLIR Gx320 24°
- 10501-0101; FLIR G620 14.5°
- 10501-0102; FLIR G620 24°
- 10601-0101; FLIR Gx620 14.5°
- 10601-0102; FLIR Gx620 24°
- 10701-0101; FLIR G635 14.5°
- 10701-0102; FLIR G635 24°
- 10801-0101; FLIR G343 14.5°
- 10801-0102; FLIR G343 24°
- 10901-0101; FLIR G346 14.5°
- 10901-0102; FLIR G346 24°
- 13801-0101; FLIR G306 14.5°
- 13801-0102; FLIR G306 24°
- 13901-0101; FLIR G304 14.5°
- 13901-0102; FLIR G304 24°
- 72502-0501; FLIR T1010 12°
- 72502-0502; FLIR T1010 28°
- 72502-0503; FLIR T1010 45°
- 72501-0101; FLIR T1020 12°
- 72501-0102; FLIR T1020 28°
- 72501-0104; FLIR T1020 28° and 12°



HDMI type C to HDMI type A cable 1.5 m

P/N: T910891ACC

© 2024, FLIR Systems, Inc.

#T910891ACC; r. AA/96121; en-US

- 72501-0105; FLIR T1020 28° and 45°
- 72501-0106; FLIR T1020 28°, 12°, and 45°
- 72501-0103; FLIR T1020 45°
- 72501-0201; FLIR T1030sc 12°
- 72501-0202; FLIR T1030sc 28°
- 72501-0203; FLIR T1030sc 45°
- 72501-0301; FLIR T1040 12°
- 72501-0302; FLIR T1040 28°
- 72501-0303; FLIR T1040 45°
- 72501-0401; FLIR T1050sc 12°
- 72501-0402; FLIR T1050sc 28°
- 72501-0403; FLIR T1050sc 45°