




KPA4CTP, Pressure Bar Copper Lug, 1-Hole

By Burndy

Catalog # [KPA4CTP](#)

Mechanical Pressure Bar Style Copper Lug, 1-Hole, 1/4" Stud, #14 Sol-#4 AWG Str, Tin Plated



Features

- High copper alloy terminal (tin-plated) for joining a wide range of cable to equipment pads or terminal blocks
- Tongue and body are 1-piece design, pressure bar equalizes pressure over the conductor and prevents the screw from cutting into the cable

Application

For Joining A Wide Range Of Copper Cable To Equipment Pads Or Terminal Blocks

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Str Size	• 14 AWG • 12 AWG • 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG
Conductor Size	14-4 AWG
Conductor - Copper Solid Size	• 14 AWG • 13 AWG • 12 AWG • 11 AWG • 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG

- 5 AWG
 - 4 AWG
- CU C Str-Size
 - CU C Solid-Size

Conductor - Copper Solid Size Range 14 AWG-4 AWG

Conductor Type

Conductor - Copper Str Size Range 14 AWG-4 AWG

Configuration

Physical Attribute - Number of Screws	1
Physical Attribute - Number of Holes	1
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	0.50 in
Package Height	0.000 in
Dimension - Height mm	25.4 mm
Dimension - Height inch	1.00 in
Dimension - Height fraction	1 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	33 mm
Dimension - Hole Size mm	7 mm
Dimension - Hole Size inch	0.28 in
Dimension - Strip Length inch	9/16
Dimension - Stud Size inch	1/4
Dimension - Bolt Size fraction	1/4
Dimension - D inch	0.71 in
Dimension - N inch	0.33 in
Dimension - Length Overall inch	1.28 in

Force Related

Installation Torque Recommended in-lb	45 LBS/in
---------------------------------------	-----------

General

Trade Name	SCRULUG™
Physical Attribute - Screw Type Plated	Slot Y

Sub Brand	SCRULUG
UPC	781810802731
Type	Bolted Lugs & Terminals
Material	Copper
Plating Type	Tin
Hardware Type	5/16 Dia.Slot Robertson
UPC 14 Digit GTIN	00781810802731

Logistics

Minimum Pack Quantity	1
Pallet Quantity	39600
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)



A Hubbell brand

© 2026 Hubbell Incorporated. All rights reserved
BRDY-KPA4CTP-SPEC-EN | REV 5/2026