

VIEW WITHOUT STUFFING BOX




PANEL HOLE


AS PER MIL-DTL-38999 SERIES I & III



PANEL THICKNESS : 1,6 MIN / 6,0 MAX



A-A






TABLE 1							
SHELL SIZE	A THREAD	B	D ±0,4	E ±0,3	J +0,25/-0,00	K +0,00/-0,06	MAX ENTRY
09	11/16-24 UNEF	2,7	27,0	30,2	17,60	16,70	08
11	13/16-20 UNEF	2,7	31,8	34,9	20,96	19,59	10
13	1-20 UNEF	2,7	34,9	38,1	25,65	24,26	13
15	1 1/8-18 UNEF	2,7	38,1	41,3	28,83	27,56	15
17	1 1/4-18 UNEF	2,7	41,3	44,5	32,01	30,73	18
19	1 3/8-18 UNEF	3,5	46,0	49,2	35,18	33,91	18
21	1 1/2-18 UNEF	3,5	49,2	52,4	38,35	37,08	18
23	1 5/8-18 UNEF	3,5	52,4	55,6	41,53	40,26	18
25	1 3/4-18 UNEF	3,5	55,6	58,7	44,70	43,43	18

TABLE 2					
ENTRY SIZE	F THREAD	C MIN	G	H	CABLE ENTRY
03	M18 X 1	4,7	22	25,4	6,6 - 10,6
04	M18 X 1	6,3	22	25,4	6,6 - 10,6
05	M19 X 1	7,9	25	29,0	10,1 - 12,0
06	M23 X 1	9,5	28	32,0	10,8 - 16,3
07	M23 X 1	11,1	28	32,0	10,8 - 16,3
08	M23 X 1	12,7	28	32,0	10,8 - 16,3
09	M26 X 1	14,2	33	38,0	14,6 - 19,8
10	M26 X 1	15,8	33	38,0	14,6 - 19,8
11	M29 X 1	17,4	36	42,0	18,5 - 24,0
12	M29 X 1	19,0	36	42,0	18,5 - 24,0
13	M29 X 1	20,6	36	42,0	18,5 - 24,0
14	M34 X 1	22,2	38	44,0	22,0 - 25,0
15	M34 X 1	23,8	38	44,0	22,0 - 25,0
16	M37 X 1	25,4	42	49,0	26,0 - 28,6
17	M39 X 1	27,0	46	50,0	32,0 - 35,0
18	M40 X 1	28,6	48	55,0	33,0 - 36,0

TABLE 3	
MATERIAL/PLATING	
1-B	ALUMINIUM/CADMIUM OLIVE DRAB OVER ELECTROLESS NICKEL
1-C	ALUMINIUM/ELECTROLESS NICKEL
4-J	STAINLESS STEEL/PASSIVATE
2-Z	NICKEL ALUMINIUM BRONZE/SHOT BLASTED FOR NON-REFLECTIVE FINISH

* NOTE:

1. MATERIAL / PLATING
   OTHER OPTIONS AVAILABLE
   - PLEASE CONSULT SALES OFFICE FOR DETAILS

EXAMPLE PART NUMBER: 100P3230-21-11-1-C	
100P3230=	POLAMCO SERIES
21=	SHELL SIZE (SEE TABLE 1)
11=	ENTRY SIZE (SEE TABLE 2)
1=	MATERIAL: ALUMINIUM (SEE TABLE 3)
C=	PLATING: ELECTROLESS NICKEL (SEE TABLE3)

DRAWN	W.RUST	DATE 02/03/2012	3RD ANGLE PROJECTION NOT TO SCALE	POLAMCO LTD	WESTON LOCK LOWER BRISTOL ROAD BATH BA2 1EP	PAGE 1	UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS IN MILLIMETRES
SALES APPR	J-L.MODJTABAI	02/03/2012					
DESIGN APPR			THIS DRAWING IS COPYRIGHTANDTHE PROPERTY OF POLAMCO LTD IT MUST NOT BE COPIED, USED FOR MANUFACTURE OR OTHERWISE DISCLOSED WITHOUT PRIOR WRITTEN CONSENT OF THE COMPANY.	ASSY USED ON: BASED ON MIL-DTL-38999 SERIES I		MATERIAL: SEE ABOVE
QUAL APPR				TITLE: PANEL MOUNT BULKHEAD STUFFING BOX		NCAGE CODE U5792
ISSUE 1	DCR 4633			PART NUMBER: 100P3230-**-**-*-*		DRAWING NO: P20278
WEIGHT —	GENERAL TOL LINEAR +/-0.1MM ANGULAR +/- 1°					

Downloaded from Arrow.com.