



**Part Number :** [15045104](#)

**Product Description :** 2.54mm SL Interim Clip, 10 Circuits, Polarized

**Series Number :** 70013

**Status :** Active

**Product Category :** Connector Accessories

**Engineering Part Number :** 70013-1010



---

## Documents and Resources

### Drawings

[015045104\\_sd.pdf](#)

[700130000-PK-000.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)


### Specifications

[PS-70400-001.pdf](#)

---

## Product Environment Compliance

### Compliance

|                    |   |
|--------------------|---|
| GADSL/IMDS         | Not Relevant  |
| China RoHS         |  per SJ/T 11365-2006 |
| EU ELV             | Not Relevant  |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21  |
| REACH SVHC         | Not Contained per D(2025)7771-DC (04 Feb 2026)  |
| EU RoHS            | Compliant per EU 2015/863   |

### [Compliance Statements](#)

- EU RoHS

- REACH SVHC
- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

---

## Part Details

### General

|                |  |
|----------------|--|
| Status         | Active   |
| Category       | Connector Accessories                          |
| Series         | 70013  |
| Description    | 2.54mm SL Interim Clip, 10 Circuits, Polarized |
| Component Type | Interim Clip                                   |
| Product Name   | SL   |
| UPC            | 800753605107                                   |

### Agency

|     |         |
|-----|---------|
| CSA | LR19980 |
| UL  | E29179  |

### Physical

|                     |           |
|---------------------|-----------|
| Circuits (Loaded)   | 10        |
| Circuits (maximum)  | 10        |
| Color - Resin       | Black     |
| Flammability        | 94V-0     |
| Lock to Mating Part | Yes       |
| Material - Resin    | Polyester |
| Net Weight          | 1.550/g   |

|                          |     |
|--------------------------|-----|
| Number of Rows           | 2   |
| Packaging Type           | Bag |
| Polarized to Mating Part | Yes |

### Solder Process Data

|                              |     |
|------------------------------|-----|
| Lead-Free Process Capability | N/A |
|------------------------------|-----|

### Mates With / Use With

#### Use with Part(s)

| Description   | Part Number  |
|---|--------------|
| SL Single Row Crimp Housings and CPA Retainers                    | <u>70066</u> |
| SL Female Terminals   | <u>70058</u> |
| SL Single Row Female Insulation Displacement Connector Assemblies | <u>70400</u> |
| SL Single Row Female Receptacles                                  | <u>70430</u> |
| SL Dual Row Crimp Housings  | <u>70450</u> |

---

This document was generated on Apr 11, 2026