

[Printer Labels](#) / [BradyPrinter S3100 Labels](#) /

B30 Series Raised Panel Polyester Labels

B30 Series Raised Panel Polyester Labels



Product Highlights

Label/Tape Size:

0.59 in H x 1.77 in W

Color:


White

Part Number:

B30EP-172-593-WT

ADD TO CART

1



Add To Favorites

People Who
Viewed This
Item Ultimately
Bought



Calculate how many labels you can print with one ribbon



Overview

Raised panel Adhesive-Taped Polyester (B-593) labels are designed for patch panel identification, external push-buttons, switches and internal connection points.

- Can be used as rating and serial plates using alphanumerics that require nameplate quality
- Aggressive adhesive and solvent resistance makes them a great replacement for engraved tags
- UL approved

- Service temperature of -4 to 212° F (-20 to 100° C)

Specifications

Average Outdoor Durability	10 Years
Material Number	B-593
Country of Origin	MX - All trade information (i.e. Country of Origin, Harmonized Schedule code, and/or Export Control Classification Number) and related assistance provided by Brady Corporation and its affiliates is provided for informational purposes only and is subject to change without notice. Any use of such information by you is without recourse to Brady Corporation or its affiliates and is at your own risk. This information is not provided as legal advice or as a substitute for obtaining specific legal advice. If you have any questions regarding your specific situation, you should consult your attorney.
Catalog Page #	412
Corner Type	Rounded Corners
Dimensions	0.59 in H x 1.77 in W
UOM	Roll of 450 Labels
Finish	Gloss
Indoor or Outdoor Use	Outdoor Use
Label/Tape Size	0.59 in H x 1.77 in W
Maximum Service Temperature °F	212 °F
Minimum Service Temperature °F	-4 °F
Product Number	118021
UPC	754473211059
Quantity per Roll	450
Quantity per Row	1
Thickness	0.0256 in
Trade Name	B30
Unit Price	/Label
UNSPSC	55121612
Adhesive Type	Acrylic-Foam Backed
Applications	Engrave Plate Substitutes for Panel ID
Color	White
For Use with Printer	BBP®30 Label Printer, BBP®31 Sign and Label Printer, BBP®33 Label Printer, BBP®35 Multi-Color Sign and Label Printer, BBP®37 Color & Cut Sign and Label Printer, BradyPrinter S3100
Label/Media Format	Roll
Label Properties	Heat Resistant Labels, Permanent Adhesive Labels

Material	Polyester
Material Properties	Raised
Printer and Label Applications	Electrical, General Identification, Inspection Repair, Rating & Name Plates
Print Technology	Thermal Transfer
Resistance Properties	Abrasion-Resistant, Chemical-Resistant, Corrosion-Resistant, Humidity-Resistant
Shape	Rectangle
Suggested Ribbon Series	R4400, R6000



B30 Series R6600 Printer Ribbon, Black

Part Number:
B30-R6600

Solutions

[Floor Marking Guide](#)
[GHS Label Compliance](#)
[Lockout Tagout Compliance](#)
[Arc Flash Labeling Requirements](#)
[Cable and Wire Label Options](#)
[Product and Barcode Labeling](#)

Services

[Lockout Tagout Services](#)
[Arc Flash Services](#)
[Confined Space Services](#)
[Software Programming & Integration](#)
[Label Template & File Conversion](#)
[Printer Use & Training](#)
[Printer Preventative Maintenance](#)
[Toll and Custom Coating](#)
[Authentication & Tracking Services](#)

Help

[Contact Us](#)
[Website Feedback](#)
[Knowledge Center](#)
[Printer Drivers & Firmware](#)
[Brady Software Updates](#)
[Safety Data Sheets](#)
[Technical Data Sheets](#)
[WEEE-RoHS Compliance](#)
[Product Certification](#)
[Printer Registration](#)

Resources

[Find a Distributor](#)
[Design Custom Safety Signs](#)
[Create Custom THT Labels](#)
[Printer Selection Tool](#)
[Label Selection Tool](#)
[Digital Catalog](#)
[Request a Catalog](#)
[Interactive Facility Map](#)
[EPA e-Manifest Update](#)

Corporate

[About](#)
[Careers](#)
[Investors](#)
[Privacy Policy](#)
[Terms and Conditions](#)
[Terms of Use](#)
[ISO Certificates](#)


Other Brady Sites

[Distributor Portal](#)
[International Sites](#)
[Safety Services & Software](#)
[Brand Protection Solutions](#)

Contact

6555 W. Good Hope Rd.
Milwaukee, WI 53223
Phone: 888-250-3082
Hours: 7am-6pm CT
Monday - Thursday;
Friday 7am-5pm CT

Brady (NYSE:BRC) is a manufacturer of complete solutions that identify and protect people, products and places. Brady's products help customers increase safety, security, productivity and performance and include high-performance labels, signs, safety devices, printing systems and software.



2019 © Brady Worldwide, Inc.

