

Universal Reversible USB 2.0 Super Slim Cable (Reversible A to B M/M), 6 ft.

MODEL NUMBER: UR022-006-SLIM



Description

Tripp Lite's UR022-006-SLIM, 6-ft. USB 2.0 A/B device cable features a Super Slim design that is more than 35% thinner than standard USB 2.0 A/B device cables. It also includes a Universal / Reversible "A" connector, which takes the guesswork out of which way to position the "A" connector for plugging. It supports USB 2.0 data transfer rates up to 480Mbps, and is backward compatible - can be used with older USB1.1 applications as well. All Tripp Lite USB 2.0 cabling includes superior foil shielding for reliable, error-free data communications. Features nickel plated connectors and gold plated copper contacts for superior conductivity. The cable is manufactured with molded connectors and integral strain relief for extra durability and long life.

Features

- Super Slim design...over 35% thinner than standard USB A/B device cables
- Universal, Reversible "A" connector allows plugging in any direction
- Supports USB 2.0 data transfer rates up to 480Mbps
- Backward compatible with previous USB generations
- Gold plated contacts and molded ends provide a lifetime of use
- 30AWG Data Pair, 30AWG Power pair

Specifications

OVERVIEW	
UPC Code	037332188137
Technology	USB 2.0 (High Speed); USB

Highlights

- Super Slim design...over 35% thinner than standard USB A/B device cables
- Universal, Reversible "A" connector allows plugging in any direction
- Supports USB 2.0 data transfer rates up to 480Mbps

System Requirements

- Any USB device requiring a USB cable
- USB 2.0 performance only when used with a USB 2.0 device and USB 2.0 controller

Package Includes

- Universal Reversible USB 2.0 A-Male to B-Male Super Slim Device Cable - 6ft



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

PHYSICAL	
Color	Black
Cable Length (ft.)	6
Cable Length (m)	1.8
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (kg)	0.05
Shipping Weight (lbs.)	0.11
ENVIRONMENTAL	
Operating Temperature Range	-10 to 75° C (14 to 167° F)
Storage Temperature Range	-20 to 80° C (-4 to 176° F)
CONNECTIONS	
Side A - Connector 1	REVERSIBLE USB A (MALE)
Side B - Connector 1	USB B (MALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>