

# FBP-3/4 TR - Cover profile

3069922

<https://www.phoenixcontact.com/us/products/3069922>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cover profile, depth: 32 mm, width: 74.1 mm, height: 65 mm, color: transparent



## Commercial data

Item number	3069922
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BE06
Product key	BE6113
GTIN	4055626136899
Weight per piece (including packing)	54.1 g
Weight per piece (excluding packing)	54.1 g
Customs tariff number	39162000
Country of origin	PL

# FBP-3/4 TR - Cover profile

3069922

<https://www.phoenixcontact.com/us/products/3069922>



## Technical data

### Product properties

Product type	Cover profile
Insulation characteristics	
Overvoltage category	III

### Dimensions

Width	74.1 mm
Height	65 mm
Depth	32 mm

### Material specifications

Color	transparent
Flammability rating according to UL 94	V0
Insulating material group	I
Insulating material	PVC

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

# FBP-3/4 TR - Cover profile

3069922

<https://www.phoenixcontact.com/us/products/3069922>



## Classifications

### ECLASS

ECLASS-13.0	27141190
ECLASS-15.0	27141190

### ETIM

ETIM 9.0	EC002848
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# FBP-3/4 TR - Cover profile



3069922  
<https://www.phoenixcontact.com/us/products/3069922>

## Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)