



Part Number : [1301530111](#)

Product Description : Safeway In-Line Commercial GFCI, Permanent Mount, Single Phase, Manual Reset, Flying Leads, 20A, 120V, 0.61m (2.0') Cord Length

Series Number : 130153

Status : Active

Product Category : Power Distribution

Engineering Part Number : 20051-1



Documents and Resources

Drawings

[1301530111_sd.pdf](#)

Product Environment Compliance

Compliance

| | |
|--------------------|--|
| GADSL/IMDS | Not Relevant |
| China RoHS | Not Reviewed per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Reviewed per IEC 61249-2-21 |
| REACH SVHC | Not Reviewed per D(2025)6375-DC (05 Nov 2025) SCIP:d282de07-64cd-431f-ae7d-894ea99ec40b |
| EU RoHS | Compliant with Exemption 6(c) per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

| | |
|--------------------|---|
| Status | Active |
| Category | Power Distribution |
| Series | 130153 |
| Description | Safeway In-Line Commercial GFCI, Permanent Mount, Single Phase, Manual Reset, Flying Leads, 20A, 120V, 0.61m (2.0') Cord Length |
| Enclosure Rating | NEMA 4 |
| NEMA Configuration | N/A |
| Product Name | Safeway |
| Type | GFCI Commercial Duty, Single Phase |
| UPC | 78678828417 |

Agency

| | |
|-----|--------|
| CSA | LR6837 |
| UL | E66308 |

Electrical

| | |
|-------------------------------|-------------|
| Current - Maximum per Contact | 20.0A |
| GFCI | Yes-In-line |
| GFCI Reset | Manual |
| Ground Continuity Monitor | No |
| Open Neutral Relay | Yes |
| Voltage - Maximum | 120V AC |

Physical

| | |
|-----------------------|-------------------------|
| Cord Diameter | 10.92mm (.430") |
| Cord Grip Body Size | Internal Double C-Clamp |
| Cord Length | 0.61m (2.0') |
| Cord Type | 12/3 SJTW |
| Feed-Thru | Yes |
| Flip Lid | No |
| Material - Housing | Nylon |
| Mounting Style | Portable |
| Net Weight | 108.501/g |
| Number of Receptacles | 0 |
| Packaging Type | Bag |
| Receptacle Type | N/A |

This document was generated on Jan 04, 2026