

**Part Number :** [395040008](#)

**Product Description :** 3.50mm Pitch Eurostyle Horizontal Plug, with Retention Screws, 8 Circuits

**Series Number :** 39504

**Status :** Active

**Product Category :** Terminal Blocks and Barrier Strip



---

## Documents and Resources

### Drawings

[395040008\\_sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)


### Specifications

[PS-39500-001-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)7771-DC (04 Feb 2026) SCIP:4605aaff-d857-4047-90c9-a6cd06cbd0b3
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC

- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

## Part Details

### General

Status	Active
Category	Terminal Blocks and Barrier Strip
Series	39504
Description	3.50mm Pitch Eurostyle Horizontal Plug, with Retention Screws, 8 Circuits
Application	Wire-to-Board
Component Type	Plug
Product Name	Eurostyle Pluggable
Type	PCB Terminal Blocks and Connectors
UPC	822350440097

### Agency

UL	E48521
----	--------

### Electrical

Current - Maximum per Contact	8.0A
Voltage - Maximum	300V

### Physical

Circuits (Loaded)	8
Circuits (maximum)	8

Color - Resin	Black
Entry Angle	Vertical
Lock to Mating Part	Yes
Net Weight	6.160/g
Number of Rows	1
Orientation	N/A
Panel Mount	No
PCB Retention	N/A
Pitch - Mating Interface	3.50mm
Pitch - Termination Interface	3.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C
Wire Size (AWG)	16, 18, 20, 22, 24, 26, 28, 30
Wire Size mm <sup>2</sup>	0.05-1.31

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
3.50mm Pitch Eurostyle Vertical PCB Headers	<u><a href="#">39505</a></u>
3.50mm Pitch Eurostyle Horizontal PCB Headers	<u><a href="#">39506</a></u>
Mates With	Most 3.50mm Pitch Industry Standard PCB Headers

---

This document was generated on Apr 23, 2026