

# Product data sheet

Specifications



## APC NetShelter Basic Rack PDU, Zero U, 5.7kW, 120 and 208V, 21 5-20 and 6 L6-20 outlet

AP7563

### Overview

Lead time Usually in Stock

### Main

Colour	Black
Product or component type	PDU
PDU type	Basic
Cord length	0.9 m
Number of cables	1
Provided equipment	Installation guide Rack mounting brackets Toolless mounting kit

### Complementary

Input Voltage	208 V 3 phases
Height	177.8 cm
Width	5.6 cm
Output Voltage	120 V 208 V
Depth	4.4 cm
Net weight	5.46 kg
Mounting location	Side
Mounting preference	No preference
Input Plug Type	NEMA L21-20P
Mounting mode	Rack-mounted
Rack units	0U
Mounting position	Vertical
[In] rated current	16 A
Input current limits	20 A
Load capacity	5700 VA
Network frequency	50/60 Hz
Outlet type and quantity	21 NEMA 5-20R 6 NEMA L6-20R

### Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

<b>Product certifications</b>	cUL listed UL listed
<b>Standards</b>	CSA C22.2 No. 60950-1-03 UL 60950-1
<b>Ambient air temperature for operation</b>	0...45 °C
<b>Relative humidity</b>	5...95 %
<b>Operating altitude</b>	0...10000 ft
<b>Ambient air temperature for storage</b>	-25...65 °C
<b>Storage Relative Humidity</b>	5...95 %
<b>Storage altitude</b>	0...15240 m

## Packing Units

<b>Unit Type of Package 1</b>	PCE
<b>Number of Units in Package 1</b>	1
<b>Package 1 Height</b>	213.4 cm
<b>Package 1 Width</b>	12.7 cm
<b>Package 1 Length</b>	15.2 cm
<b>Package 1 Weight</b>	6.36 kg

## Contractual warranty

<b>Warranty</b>	2 years repair or replace
-----------------	---------------------------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

### Environmental footprint

Environmental Disclosure

[Product Environmental Profile](#)

## Use Better

### Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
<a href="#">EU RoHS Directive</a>	Compliant
REACH Regulation	<a href="#">REACH Declaration</a>
Halogen-free status	Product contains halogen above thresholds

### Energy efficiency

Energy Efficiency Optimized	Energy efficient product
-----------------------------	--------------------------

## Use Again

### Repack and remanufacture

End of life manual availability	<a href="#">End of Life Information</a>
Take-back	Yes

Image of product / Alternate images

Alternative

---

