

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Thermal transfer printer for card materials, including Euro/US power cable and USB cable. User manual printed in German and English. Magazine for UCT-TM... sheets and magazines for US... cards. One packing unit each UCT-TM 6, US-EMLP (85,6x54), ink ribbon = 50 m

Product description

THERMOMARK CARD 2.0 prints markers in card format for top quality terminal, wire, cable, equipment and plant marking applications. You can easily create high-quality printed labels and markers.

Your advantages

- Maintenance-free operation with proven thermal transfer printer technology
- Easy to control with the PROJECT COMPLETE software
- Automatic material detection prevents printing errors
- Fast, high-quality, and durable printing; printing time for one card is less than 8 seconds
- Easy and intuitive operation via touch color display
- For all UniCard (UCT) and UniSheet (US) materials
- USB and Ethernet connections

Commercial data

Item number	1085267
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG01
Product key	BG1221
Catalog page	Page 35 (C-3-2019)
GTIN	4055626834931
Weight per piece (including packing)	9,940 g
Weight per piece (excluding packing)	9,908 g
Customs tariff number	84433210
Country of origin	DE

THERMOMARK CARD 2.0 - Thermal transfer printer



1085267

<https://www.phoenixcontact.com/us/products/1085267>

Technical data

Product properties

Product type	Printing system
Scope of delivery	Thermal transfer printer for card materials, including Euro/US power cable and USB cable. Manual printed in German and English. Magazine for UCT-TM... sheets and magazines for US-... cards. One packing unit each UCT-TM 6, US-EMLP (85,6x54), ink ribbon: 50 m

Marking

Identification technology	Thermal transfer for sheets and cards
---------------------------	---------------------------------------

Device properties

Print width	104 mm
Print resolution	300 dpi
Operating system	MS Windows Vista, MS Windows 7 (32/64-bit), MS Windows 8 (32/64-bit), MS Windows 8.1 (32/64-bit), MS Windows 10 (32/64-bit), Server 2008, Server 2008 R2, Server 2012, Server 2012 R2

Electrical properties

Supply

Supply voltage range	100 V AC ... 240 V AC (50 Hz ... 60 Hz)
----------------------	---

Interfaces

Interface	10/100 Mbps Ethernet, USB 2.0
-----------	-------------------------------

Dimensions

Width	254 mm
Height	194 mm
Length	325 mm

Material specifications

Material Plastic signs	UCT
	US
	UM









Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	5 °C ... 35 °C
---------------------------------	----------------

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1085267>

	IECEE CB Scheme Approval ID: DK-81168-M1-UL
	EAC Approval ID: RU D-DE.GB09.B.00141
	IECEE CB Scheme Approval ID: DK-81169-M1-UL
	UL Listed Approval ID: E140143
	CCC Approval ID: 2019010904255703
	cUL Listed Approval ID: E140403
	KC Approval ID: R-R-YG3-TC2_0
	EAC-RoHS Approval ID: RU D-DE.HB49.B.00023
	UAE-RoHS Approval ID: 13775_E22-04-033962
	cULus Listed

Classifications

ECLASS

ECLASS-11.0	19140104
ECLASS-12.0	19140104
ECLASS-13.0	19140104

ETIM

ETIM 9.0	EC001684
----------	----------

UNSPSC

UNSPSC 21.0	43212100
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(c)-I
China RoHS	
Environment friendly use period (EFUP)	EFUP-10
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)

THERMOMARK CARD 2.0 - Thermal transfer printer



1085267

<https://www.phoenixcontact.com/us/products/1085267>

Accessories

THERMOMARK-RIBBON 110/50-TC - Ink ribbon

0801384

<https://www.phoenixcontact.com/us/products/0801384>



Ink ribbon, for THERMOMARK CARD for printing product groups UCT..., US..., and UM..., length: 50 m, roll length: 50 m, width: 110 mm, color: black

THERMOMARK-RIBBON 110-TC - Ink ribbon

0801371

<https://www.phoenixcontact.com/us/products/0801371>



Ink ribbon, for THERMOMARK CARD for printing product groups UCT..., US..., and UM..., length: 300 m, roll length: 300 m, width: 110 mm, color: black

THERMOMARK CARD 2.0 - Thermal transfer printer



1085267

<https://www.phoenixcontact.com/us/products/1085267>

TM-RIBBON 110 WH 100 - Ink ribbon

0804661

<https://www.phoenixcontact.com/us/products/0804661>



Ink ribbon, For THERMOMARK roll printers and THERMOMARK CARD for printing material-off-the-roll product groups: EML ..., EMLP ..., EMLF ..., PML-M . . ., WMTB HF-HP..., WMS-2 HF ... RD and US-material product groups: US-EML(S)P ..., US-EMLP-HA ..., US-EM(S)P ..., US-WMT ..., US-WMTB ..., US-PML-M ..., US-EMLF ..., length: 60 m, roll length: 60 m, width: 110 mm, color: white

TMP-US-MAG1 - Magazine

0803341

<https://www.phoenixcontact.com/us/products/0803341>



Magazine, For THERMOMARK CARD and THERMOMARK PRIME, for accommodating US cards, length: 0.166 m, width: 114 mm, height: 10 mm

THERMOMARK CARD 2.0 - Thermal transfer printer



1085267

<https://www.phoenixcontact.com/us/products/1085267>

TMP-UCT-MAG1 - Magazine

0803342

<https://www.phoenixcontact.com/us/products/0803342>



Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-TM..., UCT1(U)-TM..., UCT5-TM..., UCT-EM (5x10), UCT-EM (6x10), length: 0.166 m, width: 114 mm, height: 11.5 mm

TMP-UCT-MAG2 - Magazine

0803343

<https://www.phoenixcontact.com/us/products/0803343>



Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-TMF..., length: 0.166 m, width: 114 mm, height: 11.5 mm

THERMOMARK CARD 2.0 - Thermal transfer printer



1085267

<https://www.phoenixcontact.com/us/products/1085267>

TMP-UCT-MAG3 - Magazine

0803344

<https://www.phoenixcontact.com/us/products/0803344>

Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-WMS..., length: 0.166 m, width: 114 mm, height: 11.5 mm



TMP-UCT-MAG4 - Magazine

0803345

<https://www.phoenixcontact.com/us/products/0803345>

Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT1-TMF..., length: 0.166 m, width: 114 mm, height: 11.5 mm



THERMOMARK CARD 2.0 - Thermal transfer printer



1085267

<https://www.phoenixcontact.com/us/products/1085267>

TMP-UM-MAG2 - Magazine

0831201

<https://www.phoenixcontact.com/us/products/0831201>

Magazine for THERMOMARK CARD and THERMOMARK PRIME, to hold UM material (UM-TMF)



TMP-UCT-MAG5 - Magazine

0803347

<https://www.phoenixcontact.com/us/products/0803347>

Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT2-TM..., length: 0.166 m, width: 114 mm, height: 11.5 mm



THERMOMARK CARD 2.0 - Thermal transfer printer



1085267

<https://www.phoenixcontact.com/us/products/1085267>

TMP-UCT-MAG6 - Magazine

0803348

<https://www.phoenixcontact.com/us/products/0803348>

Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT3-TM..., length: 0.166 m, width: 114 mm, height: 11.5 mm



TMP-UCT-MAG7 - Magazine

0803349

<https://www.phoenixcontact.com/us/products/0803349>

Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-WMT..., UCT-EM (7x10), length: 0.166 m, width: 114 mm, height: 11.5 mm



THERMOMARK CARD 2.0 - Thermal transfer printer



1085267

<https://www.phoenixcontact.com/us/products/1085267>

TMP-UCT-MAG8 - Magazine

0803350

<https://www.phoenixcontact.com/us/products/0803350>

Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-EM (20x7), UCT-EM (17,5x8), length: 0.166 m, width: 114 mm, height: 11.5 mm



TMP-UCT-MAG9 - Magazine

0803351

<https://www.phoenixcontact.com/us/products/0803351>

Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-EM (12x3,3), UCT-EM (12x6), length: 0.166 m, width: 114 mm, height: 11.5 mm



THERMOMARK CARD 2.0 - Thermal transfer printer



1085267

<https://www.phoenixcontact.com/us/products/1085267>

TMP-UCT-MAG10 - Magazine

0803352

<https://www.phoenixcontact.com/us/products/0803352>



Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-EM (30x5), length: 0.166 m, width: 114 mm, height: 11.5 mm

TMP-UCT-MAG11 - Magazine

0803353

<https://www.phoenixcontact.com/us/products/0803353>



Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-EM (17x10), length: 0.166 m, width: 114 mm, height: 11.5 mm

THERMOMARK CARD 2.0 - Thermal transfer printer



1085267

<https://www.phoenixcontact.com/us/products/1085267>

TMP-UCT-MAG12 - Magazine

0803354

<https://www.phoenixcontact.com/us/products/0803354>

Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-EM (10x8), UCT-EM (12x7), length: 0.166 m, width: 114 mm, height: 11.5 mm



TMP-UCT-MAG13 - Magazine

0803355

<https://www.phoenixcontact.com/us/products/0803355>

Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-EM (10x5), length: 0.166 m, width: 114 mm, height: 11.5 mm



THERMOMARK CARD 2.0 - Thermal transfer printer



1085267

<https://www.phoenixcontact.com/us/products/1085267>

TMP-UCT-MAG14 - Magazine

0803356

<https://www.phoenixcontact.com/us/products/0803356>

Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-EM (17x8), UCT-EM (21x8), length: 0.166 m, width: 114 mm, height: 11.5 mm



TMP-UCT-MAG15 - Magazine

0803357

<https://www.phoenixcontact.com/us/products/0803357>

Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-EM (20x9), length: 0.166 m, width: 114 mm, height: 11.5 mm



THERMOMARK CARD 2.0 - Thermal transfer printer



1085267

<https://www.phoenixcontact.com/us/products/1085267>

TMP-UCT-MAG16 - Magazine

0803358

<https://www.phoenixcontact.com/us/products/0803358>

Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-EM (17x9), length: 0.166 m, width: 114 mm, height: 11.5 mm



TMP-UCT-MAG17 - Magazine

0803360

<https://www.phoenixcontact.com/us/products/0803360>

Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-EM (18x8), length: 0.166 m, width: 114 mm, height: 11.5 mm



THERMOMARK CARD 2.0 - Thermal transfer printer



1085267

<https://www.phoenixcontact.com/us/products/1085267>

TMP-UCT-MAG18 - Magazine

0803361

<https://www.phoenixcontact.com/us/products/0803361>



Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-EM (17,5x7,5), length: 0.166 m, width: 114 mm, height: 11.5 mm

TMP-UCT-MAG19 - Magazine

0803363

<https://www.phoenixcontact.com/us/products/0803363>



Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-EM (15x10), length: 0.166 m, width: 114 mm, height: 11.5 mm

THERMOMARK CARD 2.0 - Thermal transfer printer



1085267

<https://www.phoenixcontact.com/us/products/1085267>

TMP-UCT-MAG20 - Magazine

0803364

<https://www.phoenixcontact.com/us/products/0803364>



Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-EM (10x7), UCT-WMTB (29x8), length: 0.166 m, width: 114 mm, height: 11.5 mm

TMP-UCT-MAG21 - Magazine

0803365

<https://www.phoenixcontact.com/us/products/0803365>



Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-EM (20x8), length: 0.166 m, width: 114 mm, height: 11.5 mm

THERMOMARK CARD 2.0 - Thermal transfer printer



1085267

<https://www.phoenixcontact.com/us/products/1085267>

TMP-UCT-MAG22 - Magazine

0803366

<https://www.phoenixcontact.com/us/products/0803366>

Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-EM (17,5x9), length: 0.166 m, width: 114 mm, height: 11.5 mm



TMP-UCT-MAG23 - Magazine

0803367

<https://www.phoenixcontact.com/us/products/0803367>

Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT6M-TM..., length: 0.166 m, width: 114 mm, height: 11.5 mm



THERMOMARK CARD 2.0 - Thermal transfer printer



1085267

<https://www.phoenixcontact.com/us/products/1085267>

TMP-UCT-MAG24 - Magazine

0803368

<https://www.phoenixcontact.com/us/products/0803368>

Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT6R-TM..., length: 0.166 m, width: 114 mm, height: 11.5 mm



TMP-UCT-MAG25 - Magazine

0803369

<https://www.phoenixcontact.com/us/products/0803369>

Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-WMCO ... (12x4), length: 0.166 m, width: 114 mm, height: 11.5 mm



THERMOMARK CARD 2.0 - Thermal transfer printer



1085267

<https://www.phoenixcontact.com/us/products/1085267>

TMP-UCT-MAG26 - Magazine

0803370

<https://www.phoenixcontact.com/us/products/0803370>



Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-EMP (25x6), UCT-EMP (29x8), UCT-EMP (40x17), UCT-EMP (60x15), length: 0.166 m, width: 114 mm, height: 11.5 mm

TMP-UCT-MAG27 - Magazine

0803371

<https://www.phoenixcontact.com/us/products/0803371>



Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-WMTBA (24x4), UCT-WMTBA (29x6), UCT-WMTBA (40x17), length: 0.166 m, width: 114 mm, height: 11.5 mm

THERMOMARK CARD 2.0 - Thermal transfer printer



1085267

<https://www.phoenixcontact.com/us/products/1085267>

TMP-UCT-MAG28 - Magazine

0803372

<https://www.phoenixcontact.com/us/products/0803372>



Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-WMCO ... (18x4), length: 0.166 m, width: 114 mm, height: 11.5 mm

TMP-UCT-MAG29 - Magazine

0803373

<https://www.phoenixcontact.com/us/products/0803373>



Magazine, for the THERMOMARK PRIME and THERMOMARK CARD printer, for accommodating UCT-WMCO ... (23xX), length: 0.166 m, width: 114 mm, height: 11.5 mm

THERMOMARK CARD 2.0 - Thermal transfer printer



1085267

<https://www.phoenixcontact.com/us/products/1085267>

TMP-UCT-MAG31 - Magazine

1025505

<https://www.phoenixcontact.com/us/products/1025505>

Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-EMNP (12.5x6), length: 0.166 m, width: 114 mm, height: 11.5 mm



TMP-UCT-MAG32 - Magazine

1082129

<https://www.phoenixcontact.com/us/products/1082129>

Magazine, length: 0.166 m, width: 114 mm, height: 11.5 mm



THERMOMARK CARD 2.0 - Thermal transfer printer



1085267

<https://www.phoenixcontact.com/us/products/1085267>

TMP-UCT-MAG33 - Magazine

1082130

<https://www.phoenixcontact.com/us/products/1082130>

Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD, for accommodating UCT-EM (12x8), length: 0.166 m, width: 114 mm, height: 11.5 mm



TMP-UCT-MAG34 - Magazine

1281799

<https://www.phoenixcontact.com/us/products/1281799>

Magazine, for the THERMOMARK PRIME and the THERMOMARK CARD..., for accommodating UCT-TMC (30x8), length: 0.166 m, width: 114 mm, height: 11.5 mm



THERMOMARK CARD 2.0 - Thermal transfer printer



1085267

<https://www.phoenixcontact.com/us/products/1085267>

TMP-UM-MAG1 - Magazine

0831200

<https://www.phoenixcontact.com/us/products/0831200>

Magazine for THERMOMARK CARD and THERMOMARK PRIME, to hold UM material (UM1-TM and UM5-TM)



TMP-UM-MAG3 - Magazine

0831202

<https://www.phoenixcontact.com/us/products/0831202>

Magazine for THERMOMARK CARD and THERMOMARK PRIME, to hold UM material (UM1-TMF)



THERMOMARK CARD 2.0 - Thermal transfer printer



1085267

<https://www.phoenixcontact.com/us/products/1085267>

TMP-UM-MAG4 - Magazine

0831203

<https://www.phoenixcontact.com/us/products/0831203>

Magazine for THERMOMARK CARD and THERMOMARK PRIME, to hold UM material (UM1U-TM)



TMP-UM-MAG5 - Magazine

0803328

<https://www.phoenixcontact.com/us/products/0803328>

Magazine for THERMOMARK CARD and THERMOMARK PRIME, to hold UM material (UM2-TM)



THERMOMARK CARD 2.0 - Thermal transfer printer



1085267

<https://www.phoenixcontact.com/us/products/1085267>

TMP-UM-MAG6 - Magazine

0803329

<https://www.phoenixcontact.com/us/products/0803329>

Magazine for THERMOMARK CARD and THERMOMARK PRIME, to hold UM material (UM3-TM)



TMP-UM-MAG7 - Magazine

0803330

<https://www.phoenixcontact.com/us/products/0803330>

Magazine for THERMOMARK CARD and THERMOMARK PRIME, to hold UM material (UM6M-TM)



THERMOMARK CARD 2.0 - Thermal transfer printer



1085267

<https://www.phoenixcontact.com/us/products/1085267>

TMP-UM-MAG8 - Magazine

0803331

<https://www.phoenixcontact.com/us/products/0803331>

Magazine for THERMOMARK CARD and THERMOMARK PRIME, to hold UM material (UM6R-TM)



TMP-UM-MAG9 - Magazine

0803332

<https://www.phoenixcontact.com/us/products/0803332>

Magazine for THERMOMARK CARD and THERMOMARK PRIME, to hold UM material (UM8-TM)



THERMOMARK CARD 2.0 - Thermal transfer printer



1085267

<https://www.phoenixcontact.com/us/products/1085267>

TMP-UM-MAG10 - Magazine

0803334

<https://www.phoenixcontact.com/us/products/0803334>

Magazine for THERMOMARK CARD and THERMOMARK PRIME, to hold UM material (UM7-TM)



TMP-UM-MAG11 - Magazine

0803681

<https://www.phoenixcontact.com/us/products/0803681>

Magazine for the THERMOMARK CARD printer, for accommodating UM material UM7-TM (8x10)



THERMOMARK CARD 2.0 - Thermal transfer printer



1085267

<https://www.phoenixcontact.com/us/products/1085267>

PROJECT COMPLETE - Software

1050453

<https://www.phoenixcontact.com/us/products/1050453>



Intuitive planning and marking software for configuring terminal strips and for professional marking of marking materials for terminal blocks, conductors, cables, devices, and systems. The software is available for download

UM IA THERMOMARK CARD - Manual

2910884

<https://www.phoenixcontact.com/us/products/2910884>

Manual



THERMOMARK CARD 2.0 - Thermal transfer printer



1085267

<https://www.phoenixcontact.com/us/products/1085267>

THERMOMARK-CP - Accessories

5145371

<https://www.phoenixcontact.com/us/products/5145371>

Cleaning pen, for thermal transfer printers



CLEANING STICK - Cleaning pen

5146697

<https://www.phoenixcontact.com/us/products/5146697>

Cleaning stick for fast and efficient printhead cleaning of all Phoenix Contact thermal transfer printers.



THERMOMARK CARD 2.0 - Thermal transfer printer



1085267

<https://www.phoenixcontact.com/us/products/1085267>

TL CASE - Transport case

0800613

<https://www.phoenixcontact.com/us/products/0800613>



Transport case for THERMOMARK printers, rounded profile case with aluminum frame, including the TL CASE TROLLY

TL CASE TROLLY - Cart for printer

0803337

<https://www.phoenixcontact.com/us/products/0803337>



Trolley for the transport cases for THERMOMARK LINE and THERMOMARK ROLL X1

THERMOMARK CARD 2.0 - Thermal transfer printer



1085267

<https://www.phoenixcontact.com/us/products/1085267>

TC/TR-PACKAGE WITH FOAM - Original packaging

0801804

<https://www.phoenixcontact.com/us/products/0801804>



Original packaging for transportation

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com