

Product data sheet

Specifications



Rack PDU, Metered, ZeroU, 14.4kW, 208V, (24)C13, (4)C19, (2)L6-30R; 10 CORD

AP7899B

Overview

Lead time Usually in Stock

Main

Colour	Black
Product or component type	PDU
PDU type	Metered
Cord length	3.05 m
Number of cables	1
Provided equipment	Cord retention bracket(s) Documentation CD Installation guide Rack mounting brackets RS-232 configuration cable Toolless mounting kit

Complementary

Input Voltage	208 V 3 phases
Height	177.8 cm
Width	5.6 cm
Output Voltage	208 V
Depth	9.5 cm
Net weight	10.36 kg
Mounting location	Side
Mounting preference	No preference
Mounting mode	Rack-mounted
Rack units	0U
Mounting position	Vertical
[In] rated current	40 A
Input current limits	50 A
Load capacity	14400 VA
Network frequency	50/60 Hz
Number of input connectors	1 CS8365
Outlet type and quantity	2 NEMA L6-30R 24 IEC 60320 C13 4 IEC 60320 C19

Environment

Product certifications	cUL listed CSA Industry Canada METI Denan UL listed
Standards	FCC part 15 class A ICES-003 UL 60950
Ambient air temperature for operation	-5...45 °C
Relative humidity	5...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-25...65 °C
Storage Relative Humidity	5...95 %
Storage altitude	0.000000000...15240.000000000 m

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	205.7 cm
Package 1 Width	7.9 cm
Package 1 Length	31.1 cm
Package 1 Weight	14.32 kg

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	33455
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant with Exemptions
SCIP Number	1cdb2fed-a06f-4574-913d-8df8e70936b2
REACH Regulation	REACH Declaration
Halogen content performance	Product contains halogen above thresholds

Energy efficiency

Optimized Energy Efficiency	Energy efficient product
-----------------------------	---------------------------------

Use Again

Repack and remanufacture

Circularity Profile	End of Life Information
Removable battery	Yes
Take-back	Yes

Image of product / Alternate images

Alternative









