



**Part Number :** [5046950407](#)

**Product Description :** CP-3.3 Terminal Position Assurance (TPA) Retainer, 3.30mm Pitch, Brown, 4 Circuits

**Series Number :** 504695

**Status :** Active

**Product Category :** Connector Accessories



---

## Documents and Resources

### Drawings

[5046950407\\_sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

### Specifications

[5056050000-A01.pdf](#)

[AS-504693-001-001.pdf](#)

[AS-504693-002-001.pdf](#)

[5056050000-A00.pdf](#)

[SPK-504695-001-001.pdf](#)


[PS-504693-001-001.pdf](#)

[5056050000-000.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21

REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance

### Additional Product Compliance Information

## Part Details

### General

Status	Active
Category	Connector Accessories
Series	504695
Description	CP-3.3 Terminal Position Assurance (TPA) Retainer, 3.30mm Pitch, Brown, 4 Circuits
Component Type	Terminal Position Assurance (TPA)
Product Name	CP-3.3
UPC	887191487915

### Physical

Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Brown
Material - Resin	Polybutylene Terephthalate (PBT)
Packaging Type	Bag

Temperature Range - Operating	-40° to +105°C
-------------------------------	----------------

## Mates With / Use With

### Use with Part(s)

Description	Part Number
CP-3.3 Single Row Receptacle Housings	<u>504693</u>
CP-3.3 Single Row Plug Housings	<u>504694</u>
CP-3.3 Dual Row Receptacle Housings	<u>505605</u>
CP-3.3 Dual Row Plug Housings	<u>505606</u>

---

This document was generated on May 20, 2026