

JMACDG-12XPS Product Details

 Share  Print  Email



 Active

Military/Aerospace High Performance Relays

JMACDG-12XPS = M39016/15-115P
JMACDG-12XPS (2-1617122-6)
TE Internal Number: 2-1617122-6

Product Highlights [View All](#)

- MAD TO-5 Relay Series
- Input Voltage = 12 VDC
- Contact - Arrangement = 2 Form C, DPDT, 2 C/O
- Contact - Rated Current = 1 A
- Non Polarized, Monostable Coil - Magnetic System

Pricing & Availability 

Request Sample 

Add to My Part List 

Buy Product through Distributor 

Feedback

DocumentsFeaturesCompliance

Please Note:
Use the Product Drawing for all design activity

Product Type Features	
MOSFET Driver	Without
Mechanical Attachment	
Mounting Options	PC Board
Electrical Characteristics	
Input Voltage (VDC)	12
Contact - Rated Current (A)	1
Coil Suppression Diode	With
Coil Polarity Protection Diode	Without
Coil - Resistance (Ω)	390
Coil Power Measurement	Milliwatts
Coil - Rated Power, DC (mW)	369
Actuating System	DC
Shock	75 G's, 6ms
Vibration	30G's, 10 to 3000Hz
Termination Features	
Termination Type	Long Leads
Body Features	
Enclosure Type	Hermetically Sealed

Contact Features	
Pin Configuration	.200" x .300" Spreader Pad
Configuration Features	
Contact - Arrangement 	2 Form C, DPDT, 2 C/O
Coil - Magnetic System	Non Polarized, Monostable
Transistor Driver	Without
Industry Standards	
Government/Industry Qualification	Yes
Government/Industry Part Number	M39016/15-115P
RoHS/ELV Compliance 	Not ELV/RoHS compliant
Lead Free Solder Processes 	Not suitable for lead free processing
Approved Standards	M39016 Qualified, P Level
Conditions for Usage	
Temperature Range (°C)	-65 - +125
Other	
Series 	MAD TO-5 Relay
Brand	CII

Related Products

Not quite the product you're looking for?
[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Corporate Information

- About TE
- Investors
- News Room
- Supplier Portal
- Careers
- Terms & Conditions
- Privacy Policy
- Global Accessibility Statement

Quick Links

- Distributor Inventory
- Product Cross Reference
- Documents & Drawings
- Product Compliance Support Center
- Site Map

Customer Support

- Email or Chat With Us
- Find a Phone Number
- Knowledge Base
- Manage Your Account

Keep Me Informed

