

Part #

GO!

Keyword

GO!

[Home](#) [About](#) [Distributor Locator](#) [FAQs](#) [Contact](#)

NTE Electronic Components

AC-DC Adapters

Binding Posts & Banana
Sockets **NEW PRODUCT!**

Bulbs **NEW PRODUCT!**

Cable/Wire-Ties/
Bundle Management
NEW ITEMS!

Capacitors

Circuit Protection

Clips/Test Leads

Fans

Fuses

Heat Shrink Tubing

LED Strips/EL Wire/
LED Lamps

Optoelectronic Devices

Pots/Trimmers/
Knobs/Dials

Relays/Contactors

Resistors

Semiconductors

Solder Wick

Switches **NEW TYPES!**

Terminal Blocks

Terminals & Connectors

Wire

ECG Consumer/ Commercial Products

Antenna Rotors

Chemicals

Heat Guns

Infrared Thermometer

Solder Irons/De-Soldering
Tools **NEW TYPES!**

Surge Protectors

Test Equipment

Wireless Security &
Inspection Cameras

Master Distributed Lines

Amphenol RF /
Connex: Connectors

CML: Optoelectronic
Products

Chemtronics **NEW LINE!**

Coast: LED Flashlights

Kester Solder Products

Plato: Soldering Tools,
Tips, & Accessories

Samlex: Power
Inverters

SureHold: Glues and
Adhesives

Techspray: Chemicals

WH Series

APPLICATIONS:

- Internal wiring of electrical and electronic equipment
- Internal wiring of panels, meters, computers, business machines, appliances, & control panels
- Point-to-point wiring where 300V is required
- 6 Amp Max.

FEATURES:

- Available in 26, 24, 22, 20, 18, & 16 AWG
- Tin plated copper conductor
- 16 & 18 AWG is 16 strand, 20 AWG is 10 strand, all other gauges are 7 strand
- Insulation thickness = 1/64"
- UL Style 1007
- CSA TR-64-1569
- Passes UL VW-1.S vertical flame test
- OSHA acceptable

SPECIFICATIONS:

- **Voltage Rating:** 300 Volts
- **Insulation:** P.V.C.
- **Max. Temperature:** 90°C
- **Colors:** Black, Brown, Red, Orange, Yellow, Green, Blue, Violet, Gray, White
- **Spools:** 25 and 100 feet

[Back](#)



Wire Links

Hook Up Wire

- Automotive/Truck Wire
- PTFE (Teflon) Wire
- Hook-Up Wire, 300V
- Hook-Up Wire, 600V

Speaker Wire

- Speaker Wire
- High Performance Speaker Cable
- Bonded Multi-Purpose Wire

Multi-Conductor Cable

- 2 Conductor
- 3 Conductor
- 4 Conductor

Miscellaneous Wire

- Magnet Wire
- Test Lead Wire
- Jumper Wire
- Assortment Kits **NEW!**

Accessories

- Pre-Loaded Wire Dispensers

Related Documents

Wire Brochure (PDF)

Application Notes (PDF)

NTE Cable Ties

[Home](#)
[Distributor Locator](#)
[FAQs](#)

[About](#)
[Environmental](#)
[QUICKCross Download](#)

[Contact](#)
[Manufacturing Disclaimer](#)

[Sitemap](#)
[Privacy Policy](#)



**Follow NTE on
Facebook and Twitter**