



MS593-10*

DRAWN-SEAMLESS EMI/RFI SHIELD

*OPTIONAL SHIELD CONFIGURATIONS

		
2-PIECE SHIELD COVER	2-PIECE SHIELD FRAME	1-PIECE SHIELD

ITEM P/N	ITEM DESCRIPTION	MATERIAL
MS593-10C	2-PIECE EMI/RFI SHIELD COVER	TIN-PLATED STEEL
MS593-10F	2-PIECE EMI/RFI SHIELD FRAME	TIN-PLATED STEEL
MS593-10S	1-PIECE EMI/RFI SHIELD	TIN-PLATED STEEL
MS593-10C-NS	2-PIECE EMI/RFI SHIELD COVER	NICKEL-SILVER
MS593-10F-NS	2-PIECE EMI/RFI SHIELD FRAME	NICKEL-SILVER
MS593-10S-NS	1-PIECE EMI/RFI SHIELD	NICKEL-SILVER

TIN-PLATED STEEL: CRS ELECTROLYTIC TINPLATE
NICKEL-SILVER: UNS C77000 / UNS C73500



SHIELD CONFIGURATION:

MATERIAL:

© MASACH TECH LTD.
22 HAGANAN, MODIIN 7169513 ISRAEL
T: (+972) 8-9754681 / F: (+972) 8-9754682
info@masach.com / www.masach.com

SHIELD TYPE:





1 INCH 10 MM

MMGS / PRINT 1:1 / A4

This product has been designed and manufactured by © Masach Tech Ltd. The use of this product in any type of electronic device or application is not under Masach Tech Ltd. liability.

[BACK TO TOP](#)

Technical drawing of a rectangular plate. The length is dimensioned as 59.9 and the width as 21.2. The drawing shows the top and side views of the plate, which has rounded corners and a series of small holes along the edges.




Technical drawing of a rectangular plate with the following dimensions and annotations:

- Overall width: 59.0
- Overall height: 20.3
- Inner width: 50.0
- Inner height: 16.0
- Top-left corner radius: R1.25
- Distance from top edge to centerline: 1.6
- Distance from right edge to centerline: 0.8
- Distance from right edge to centerline (Recommended): 1.5 Recommended




MMGS / PRINT 1:1 / A4

Downloaded from [Arrow.com](https://www.arrow.com).



	SHIELD CONFIGURATION:		MATERIAL:	
	1-PIECE EMI/RFI SHIELD		TIN-PLATED STEEL ⁽¹⁾	
	NOTE: (1) CRS ELECTROLYTIC TINPLATE (2) GENERAL TOLERANCE (+/-) 0.2MM			
© MASACH TECH LTD. 22 HAGANAN, MODIIN 7169513 ISRAEL T: (+972) 8-9754681 / F: (+972) 8-9754682 info@masach.com / www.masach.com	SHIELD TYPE:			1 INCH 10 MM
	DRAWN-SEAMLESS EMI/RFI SHIELD			
	MMGS / PRINT 1:1 / A4			


This product has been designed and manufactured by © Masach Tech Ltd. The use of this product in any type of electronic device or application is not under Masach Tech Ltd. liability.




 Masach	SHIELD CONFIGURATION:		MATERIAL:		
	2-PIECE EMI/RFI SHIELD		NICKEL-SILVER ⁽¹⁾		
	NOTE: (1) UNS C77000 / UNS C73500 (2) GENERAL TOLERANCE (+/-) 0.2MM				
© MASACH TECH LTD. 22 HAGANAN, MODIIN 7169513 ISRAEL T: (+972) 8-9754681 / F: (+972) 8-9754682 info@masach.com / www.masach.com	SHIELD TYPE:		 RoHS Compliant  REACH Compliant	1 INCH 10 MM	
	DRAWN-SEAMLESS EMI/RFI SHIELD				
				MMGS / PRINT 1:1 / A4	


This product has been designed and manufactured by © Masach Tech Ltd. The use of this product in any type of electronic device or application is not under Masach Tech Ltd. liability.

[BACK TO TOP](#)



	SHIELD CONFIGURATION:		MATERIAL:	
	1-PIECE EMI/RFI SHIELD		NICKEL-SILVER ⁽¹⁾	
	NOTE: (1) UNS C77000 / UNS C73500 (2) GENERAL TOLERANCE (+/-) 0.2MM			
© MASACH TECH LTD. 22 HAGANAN, MODIIN 7169513 ISRAEL T: (+972) 8-9754681 / F: (+972) 8-9754682 info@masach.com / www.masach.com	SHIELD TYPE:		 	 
	DRAWN-SEAMLESS EMI/RFI SHIELD			
	MMGS / PRINT 1:1 / A4			

This product has been designed and manufactured by © Masach Tech Ltd. The use of this product in any type of electronic device or application is not under Masach Tech Ltd. liability.



	SHIELD CONFIGURATION:		MATERIAL:	
© MASACH TECH LTD. 22 HAGANAN, MODIIN 7169513 ISRAEL T: (+972) 8-9754681 / F: (+972) 8-9754682 info@masach.com / www.masach.com	SHIELD TYPE:		 	1 INCH 10 MM
	MMGS / PRINT 1:1 / A4			

This product has been designed and manufactured by © Masach Tech Ltd. The use of this product in any type of electronic device or application is not under Masach Tech Ltd. liability.