



ITEM	QUANTITY	COMPONENTS DESCRIPTION	MATERIAL	COLOUR
1	1	24 WAY Female Housing	PBT GF15%	BLACK or GREY
2	1	TPA of DCS2 2.8 mm terminals	PBT GF30%	YELLOW
3	1	TPA of Duo Twin 0.64x0.64 terminals	PBT GF30%	YELLOW

NOTE:

A) Cavity suitable to mount the DCS2 2.8 mm female terminals
 MVL 60012811 - 60012831 - 60012841
 DPN 10751583 - 10751585 - 10751584

B) Cavity suitable to mount the 0.64 mm Duo Twin female terminals
 MVL 60080111 - 60080131
 DPN 10820519 - 10820518

C) The dimensions of 24 way male connector are showed in the customer drawing FSC 309758

FEMALE CONNECTOR PART NUMBER		COLOUR OF FEMALE HOUSING	MALE CONNECTOR PART NUMBER
17212400 (MVL) 13725605 (DPN)		BLACK	17212401 (MVL) 13725623 (DPN)
17212480 (MVL) 13764398 (DPN)		GREY	17212481 (MVL) 13764407 (DPN)

CR-16/5199	12-05-2017	A		UPDATED FRAME AND ADDED DPN	F.G. R.B. G.I.
57-06	05-09-06	03	-	Released for production	G.B. F.P. M.C.
ECN-NO. NUMERO. -ECN	DATE DD/ MM / YY DATA	REVISION REVISIONE	POSITION POSIZIONE	CHANGE DESCRIPTION DESCRIZIONE MODIFICA	DRAWN BY DISEGNATORE CHK. BY CONTROLLO APPR. BY APPROVATO
PRODUCT SPEC. SPEC. DI PRODOTTO	PACKAGING SPEC. SPEC. DI IMBALLAGGIO	APPLICATION SPEC. SPEC. DI APPLICAZIONE	COPYRIGHT DELPHI CORPORATION AND/OR ITS AFFILIATES. ALL RIGHTS RESERVED. REVISED THIS DRAWING IS THE PROPERTY OF DELPHI CORPORATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION IS PROHIBITED.		
IPS 287	17212400 17212480	IPS 288 IPS 290	SURFACE FINISH FINITURA SUPERFICIALE		
TOLERANCES TOLLERANZE	± 0.3 mm. / ± 1°	MATERIAL : MATERIALE :	See Table		
COUNTERPART Nr. CONTROPARTE Nr.	See Table		See Table		
DO NOT SCALE DRAWING DISEGNO FUORI SCALA	DATE DATA	NAME NOME	TITLE DESCRIZIONE	LOC. CODE NAZIONALITA'	IT
DRAWN BY DISEGNATORE	31/01/04	G.Stella	24 WAY FEMALE CONNECTOR		
CHECKED BY CONTROLLATO	31/01/04	F.Ciriello	ESR NO. NUMERO ESR	CAT. NO. NUMERO CAT.	See Table
APPROVED BY APPROVATO			EU030781	FSC 309757	
			FILE NAME NOME FILE	FSC 309757	
			SCALE SCALA	2:1	