

Part Number : [02091104](#)

Product Description : 2.36mm Diameter,
Standard .093" Pin and Socket Crimp Terminal, Series
1189, Female, with Tin (Sn) Plated Brass Contact, 20-14
AWG, Bag

Series Number : 1189

Status : Active

Product Category : Crimp Terminals

Engineering Part Number : 1189-A(P901)L

Packaging Alternative : [02091102](#) (Reel)



Documents and Resources

Drawings

[002091104 sd.pdf](#)

[PK-1190-003-001.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[PS-02-09-001.pdf](#)

[11890000-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC

- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	1189
Description	2.36mm Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 1189, Female, with Tin (Sn) Plated Brass Contact, 20-14 AWG, Bag
Application	Wire-to-Wire
Product Name	Standard .093"
UPC	800753746299

Physical

Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.346/g
Packaging Type	Bag
Plating min - Mating	0.508µm
Plating min - Termination	0.508µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.65-4.06mm

Wire Size (AWG)	14, 16, 18, 20
Wire Size mm ²	N/A

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Application Tooling

Global

Description	Part Number
Insertion Tool for Standard .093" Pin and Socket Terminals	<u>11020003</u>
Extraction Tool for Standard .093" Pin and Socket Terminals	<u>11030006</u>
ServiceGrade Hand Crimp Tool for Field Repair Only, 24-14 AWG	<u>638111000</u>
PremiumGrade Hand Crimp Tool for Standard .093" and .125" Pin and Socket Terminals	<u>638191100</u>
Extractor Tool for .093 and HCS-125 Product Series	<u>638240200</u>

This document was generated on Sep 23, 2026