

[→ Honeywell.com](#) [→ Automation & Control Solutions](#)[HOME](#)[ABOUT US](#)[KEY INDUSTRIES SERVED](#)[PRODUCTS & INFORMATION](#)[NEWS & EVENTS](#)[SALES & SUPPORT](#)

L

## Honeywell Sensing and Control



Search



12TW1-12L

(Home : Products : Switches &gt; MICRO SWITCH™ Toggle Switches &gt; TW )

**narrow your search****Products**

- Controls Monitoring and Lighting (352)
- Machine Safety (1701)
- Sensors (6224)
- Switches (9749)
- Wireless (39)

**Technology**

- Control and Instrumentation (1052)
- Electromechanical (9301)
- Magnetic (541)
- Optical/Infrared (1042)
- Thick Film (1764)
- More...

**new products****New Wireless Products**

Go farther. Work smarter. Explore new possibilities. Just by cutting the cord and making the switch.



Wireless Web Site  
WGLA and WPMM  
XYR6000™

[find out more](#)**white papers**

- Wireless Switches Offer Unlimited Benefit
- Basic Switches Are Not Created Equal
- Applying Precision Switches
- Sensors for Medical Devices
- New Ways to Measure Torque
- Choosing Safety Switches
- Specifying Hour Meters


**Need help?**[Click here to contact us](#)

Actual product appearance may vary.

TW Series Toggle Switch, 2 pole, 3 position, Solder terminal, Locking Lever, Military Part Number MS27754-34L

[Overview](#) [Specs](#) [Documentation](#) [Application Notes](#)**Product Specifications**

Circuitry/Operating action



Product Type  
Lever Lock



Locked out of extreme position (keyway side)

Ampere/Voltage Range (Resistive Load)	0.1 A to 5.0 A at 0.5 Vac to 115 Vac, 0.1 A to 5.0 A at 0.5 Vdc to 28 Vdc
Circuitry	DPDT
Action	3 position
Mounting	Bushing 15/32 in
Termination	Solder
MIL Spec. Number	MS27754-34L
Lever Type	Locking
UL/CSA	L117: 5 A at 125 Vac
Comment	Fine silver contacts
Availability	Global
UNSPSC Code	30211908
UNSPSC Commodity	30211908 Toggle switches
Series Name	TW

[Terms & Conditions](#) | [Privacy Statement](#) | [Site Map](#)**contacts**

Customer Service  
Technical Support  
Global Sales & Service  
View Site Demo  
Site Comments?

**meet dr. larry**

VIDEO - Dr. Larry Goldstein explains our newest and best technologies.

[Meet Dr. Larry](#)**my links**

[Login to iCOM](#)  
[Login to Rep/AD Portal](#)  
[Login to Digital University](#)

**News Center**

HONEYWELL ANNOUNCES ADDITION TO RELIALIGN™ RESIDENTIAL DOOR INTERLOCK SWITCHES THAT FEATURE RUGGED, PLASTIC HOUSING  
HONEYWELL RELEASES UNLIMITED POTENTIAL WITH NEW LIMITLESS™ WIRELESS SWITCHES  
HONEYWELL'S XYR6000 WIRELESS POSITION SENSOR ENABLES MONITORING IN HAZARDOUS AREAS AND REMOTE LOCATIONS

**MICRO SWITCH Anniversary site**