



Part Number : [2262451083](#)
Product Description : Mini-Fit Versa Color-to-Pigtail
Off-the-Shelf (OTS) Cable Assembly, 4.20mm Pitch,
Dual Row, 300.00mm Length, 8 Circuits, Red
Series Number : 226245
Status : Active
Product Category : Power and Signal Cable
Assemblies



Documents & Resources

Drawings

[2262451083 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

[Industry Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	226245
Description	Mini-Fit Versa Color-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, 4.20mm Pitch, Dual Row, 300.00mm Length, 8 Circuits, Red
Application	Power, Wire-to-Board, Wire-to-Wire
Assembly Configuration	Single Ended Connector
Connector to Connector	Mini-Fit Versa Color-to-Pigtail
Product Name	Mini-Fit Versa Color
Type	Discrete Wire Assembly
UPC	198282202813

Electrical

Current - Maximum per Contact	9.0A
Voltage - Maximum	600V

Physical

Cable Length	300.00mm
Circuits (Loaded)	8
Circuits (maximum)	8
Color - Resin	Red
Gender	Female-Pigtail

Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	44.530/g
Number of Rows	2
Overmolded	No
Packaging Type	Bag
Pitch - Mating Interface	4.20mm
Single Ended	Yes
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 1007
Wire Size (AWG)	16

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mini-Fit Jr. Dual Row Plug Housings	<u>46993</u>
Mini-Fit Vertical Dual Row Headers	<u>172447</u>

This document was generated on Sep 24, 2025